





3D VIEW



5. ORIENTATION OF "DEUTSCH" AND "-P030" TO BE OPTIONAL.



MATERIAL:
CONNECTOR: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)
PINS: COPPER ALLOY, NICKEL PLATED

3. MAXIMUM CURRENT RATING FOR THE 3 PIN BUSBAR IS 13 AMPS.




BORDERS SIGNIFY THAT EACH GROUP OF PINS (PINS 1,11,12, PINS 2,3,10,PINS 4,8,9, AND PINS 5,6,7 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR.

1. MATES WITH DT06-12SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

NOTES:



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE	02MAY2000	 TE Connectivity		
		CHK -	04MAY2000			
		APVD -	05MAY2000			
		PRODUCT SPEC 108-151009				
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DT 12 WAY RECEPTACLE KEY ARRANGEMENT A (4) 3 PIN BUSBARS-NICKEL PLATED COLOR: GREY		
		0 PLC ±		SIZE		
		1 PLC ±		CAGE CODE		
		2 PLC ±		DRAWING NO		
		3 PLC ±	±.025[0,63]	RESTRICTED TO		
		4 PLC ±		A3 00779		
		ANGLES ±		G-DT04-12PA-P030		
MATERIAL		FINISH		SCALE		
				2:1		
				SHEET 1 OF 1		
				REV C1		
				CUSTOMER DRAWING		