


SRSI 4-T15



tightening torque/thread 1.0 Nm/M 3 Inspection Test Pattern Size A 4

Type Cat.-No. Qty.p.pck.
SRSI 4-T15 41064.2 green/yellow 100

Ratings:

Dimensions TS 15
LxBxH (mm) 32x7x32
Stripped Length 9 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-4 mm²
Wire Size AWG 22-10

SRSI 2.5-T32



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.
SRSI 2.5-T32 41057.2 green/yellow 100

Ratings:

Dimensions TS 32
LxBxH (mm) 44x6x43
Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-2.5 mm²
Wire Size AWG 22-14

EARTH TERMINAL BLOCKS

SRSI 2.5-T35



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.
SRSI 2.5-T35 41058.2 green/yellow 100


Ratings:

Dimensions TS 35
LxBxH (mm) 52x6x39
Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-2.5 mm²
Wire Size AWG 22-14

SRSI 2.5-T32



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.
SRSI 2.5-T32 41055.2 green/yellow 100

Ratings:

Dimensions TS 32
LxBxH (mm) 42x6x52
Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-2.5 mm²
Wire Size AWG 22-14