




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL

PANDUIT * PART NO.	ADHESIVE BACKING	MAX. BUNDLE DIAMETER inches (mm)	WEIGHT lb(g)/100 pcs.
MACC62-A	RUBBER	0.62 (16)	0.90 (408)
MACC62-AV	HIGH BOND ACRYLIC		



PRESSURE SENSITIVE FOAM TAPE-
0.05 (1.3) THICK WITH PROTECTIVE LINER.



NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
- 2) TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER, b) PLACE IN DESIRED LOCATION, c) APPLY PRESSURE TO MOUNT.
- 3) MATERIAL:
G-90 PRE-GALVANIZED COMMERCIAL GRADE LOW CARBON STEEL. PER ASTM A 653 STEEL SHEET, ZINC COATED (GALVANIZED) BY THE HOT DIP PROCESS.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G03597GV_DC_GB02391R/00B

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

MACC62-A & MACC62-AV
METAL ADHESIVE CORD CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.1(2.5) (.XXX) ±0.02(0.5)
(.XX) ±0.05(1.3) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LGG

MAT'L:

SCALE
NOT TO SCALE

DATE
7/30/01

SEE NOTE 3

DRAWING NO.

GB02391R

DWG
A
SIZE

00B	11-6-09	TMSA	SMY	ADDED PART NUMBER MACC62-AV	GB02391R	00B	KW		
2	2/19/03	JAD		UPDATED MATERIAL DESIGNATION, ADD NOTE 3	GB02391R	2			
1	11-26-01	LGG		ADDED DIMS AND REF DIMS	GB02391R	1			
R	7-30-01	LGG		DRAWING RELEASED REPLACED SS-22006	GB02391R	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	