

## EX glands



IP 65

### Description

Cable glands with lock nut, ATEX authorisation for zones 1 and 21

### Order No.

### Packing Qty

#### KVR EX M20-MGM/sw

M20 x 1.5,  
Seal range 5 - 13 mm

227 520 01

50/1

#### KVR EX M25-MGM/sw

M25 x 1.5,  
Seal range 8 - 17 mm

227 525 01

25/1

#### KVR EX M32-MGM/sw

M32 x 1.5,  
Seal range 12 - 21 mm

227 532 01

10/1

#### KVR EX M40-MGM/sw

M40 x 1.5,  
Seal range 16 - 28 mm

227 540 01

5/1

#### KVR EX M50-MGM/sw

M50 x 1.5,  
Seal range 21 - 35 mm

227 550 01

5/1

## Classification table Abox EX / KVR EX

| Cable gland<br>Order No.                                      | M20<br>227 520 01 | M25<br>227 525 01 | M32<br>227 532 01 | M40<br>227 540 01 | M50<br>227 550 01 |
|---------------------------------------------------------------|-------------------|-------------------|-------------------|-------------------|-------------------|
| Abox <u>Ex</u> 025-2.5 <sup>2</sup> /<br>Abox <u>Ex</u> 025-L | ●                 |                   |                   |                   |                   |
| Abox <u>Ex</u> 040-4 <sup>2</sup> /<br>Abox <u>Ex</u> 040-L   | ●                 |                   |                   |                   |                   |
| Abox <u>Ex</u> 060-6 <sup>2</sup> /<br>Abox <u>Ex</u> 060-L   | ●                 | ●                 |                   |                   |                   |
| Abox <u>Ex</u> 100-10 <sup>2</sup> /<br>Abox <u>Ex</u> 100-L  | ●                 | ●                 | ●                 |                   |                   |
| Abox <u>Ex</u> 160-16 <sup>2</sup> /<br>Abox <u>Ex</u> 160-L  | ●                 | ●                 | ●                 | ●                 |                   |
| Abox <u>Ex</u> 350-35 <sup>2</sup> /<br>Abox <u>Ex</u> 350-L  |                   | ●                 | ●                 | ●                 | ●                 |