

CABLE-D-50SUB/F/OE/0,25/S/2,0M

Order No.: 2926328

The figure shows the 25-pos. version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2926328>

Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 2 m.

Commercial data

GTIN (EAN)	4 046356 546911
sales group	I682
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 247 (NTK-2010)

Product notes

WEEE/RoHS-compliant since:
08/09/2010



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	50
Number of positions, control side	50
Number of connectors, control side	0
Number of positions, module side	50
Number of connectors, modul side	1
Fixed cable length	2 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	13.5 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;