


Model 5291A Low Thermal EMF Retractable Sheath Banana Plug, Each End Patch Cord



MATERIALS:

Retractable Sheath Banana Plug:

Plug Body: Tellurium Copper, Gold Plated.

Banana Spring: Beryllium Copper, Gold Plated

Compression Spring: Stainless Steel

Tip: Nylon, Color Matches Color of Wire

Insulation: Nylon Molded to the Plug and Wire. Color Matches Color or Wire.

Wire: 12 AWG, Stranding 7 x 38/36 Bare Copper, PVC Insulated, .144 (3,66mm) O.D.

Marking: POMONA 5291A-XX

RATINGS:

Operating Temperature: +55° C (+131° F) Max.

Operating Voltage: 1000V per IEC1010-2-031

Current: 7 Amperes

ORDERING INFORMATION: Model 5291A-XX-*

XX = Wire Length, Standard Lengths: 12" (30,48cm), 36" (91,44cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

* = Color, -0 Black, -2 Red

Ordering Example: 5291A-12-2 Patch Cord is 12" (30,48cm), Color is red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5291A-36-2](#) [5291A-36-0](#) [5291A-60-0](#) [5291A-60-2](#)