

Current refinements (click  to remove)

Search Tips

 Region  USA

 Product Family  Braided Expandable Sleeving – Flame Retardant Polyethylene Terephthalate

 Text Search: 'SE25PFR-TR0'

Your search criteria matched only one product, shown below.



- Provides continuous abrasion resistance for wires cables and tubing
- Lightweight durable protection
- Highly flexible open weave will not trap heat or humidity
- Rated for use up to 257°F (125°C)
- Allows for use with irregular shapes
- Self extinguishing meets UL VW-1
- Stock colors: Black or gray with white tracer or in white with black tracer to identify flame retardant materials.

|                               |                                                                                                                                                                                  |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part Number:                  | SE25PFRTR0                                                                                                                                                                       |
| RoHS Compliancy Status:       | Compliant                                                                                                                                                                        |
| Part Description:             | Flame Retardant Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity. |
| Material:                     | Flame Retardant Polyethylene Terephthalate                                                                                                                                       |
| Color:                        | Black                                                                                                                                                                            |
| CSA Certified:                | Yes                                                                                                                                                                              |
| UL Recognized:                | E116868                                                                                                                                                                          |
| Flammability Rating:          | UL224 VW-1                                                                                                                                                                       |
| Length Per Reel (ft.):        | 200                                                                                                                                                                              |
| Length Per Reel (m):          | 61.0                                                                                                                                                                             |
| Nominal Diameter Range (In.): | .125 to .375                                                                                                                                                                     |
| Nominal Diameter Range (mm)   | 3.2 to 9.5                                                                                                                                                                       |
| Nominal I.D. (In.):           | .25                                                                                                                                                                              |
| Nominal I.D. (mm):            | 6.4                                                                                                                                                                              |
| Temperature Range:            | -94°F to 257°F (-70°C to 125°C)                                                                                                                                                  |
| Min. Order UOM:               | RL                                                                                                                                                                               |
| Min. Order Qty.:              | 1                                                                                                                                                                                |
| BOM Qty. (# of Pkgs.)         | <input type="text" value="0"/>                                                                                                                                                   |
| Add to My Catalog             |                                                                                               |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.