

Strippers, Cutters and Crimpers

Manufactured with the needs of the professional tool user in mind, Klein strippers, cutters, and crimpers are designed to get jobs done with precision and quality.



For Professionals...
Since 1857™

KLEIN-KURVE™ Wire Strippers/Cutters

comfort grip handles



Wire looping and bending holes.

Strong gripping serrated nose for easy bending, shaping, and pulling of wire.

Coil spring provides fast self-opening action.

Double dipped comfort grips.

Handy closure lock for convenient storage.

Screw shearing holes

Precision ground stripping holes

Wire Strippers/Cutters

Additional Features:

- Easy-to-read markings
- Precision shear-type blades
- Cleanly shears 6-32 and 8-32 screws
- Cat. No. 11054GLW features glow in the dark grips to easily locate your tool in dark or low lit areas

SOLID
6 - 16 AWG

STRANDED
10 - 18 AWG



11054



Glow in the Dark Grips

11054GLW

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Screw Shearing	Weight
11053	Blue/Red	7-1/8" (181.0 mm)	6 - 12 AWG Stranded (10 mm ² - 2.5 mm ²)	6-32 and 8-32	5.4 oz. (153 g)
11054	Blue/White	7-1/8" (181.0 mm)	8 - 16 AWG Solid (8.4 mm ² - 1.3 mm ²), 10 - 18 AWG Stranded (5.3 mm ² - 0.82 mm ²)	6-32 and 8-32	5.4 oz. (153 g)
11054GLW	Glow	7-1/8" (181.0 mm)	8 - 16 AWG Solid (8.4 mm ² - 1.3 mm ²), 10 - 18 AWG Stranded (5.3 mm ² - 0.82 mm ²)	6-32 and 8-32	5.4 oz. (153 g)
11055	Blue/Yellow	7-1/8" (181.0 mm)	10 - 18 AWG Solid (4.0 mm ² - 0.75 mm ²), 12 - 20 AWG Stranded (2.5 mm ² - 0.50 mm ²)	6-32 and 8-32	5.4 oz. (153 g)
11057	Blue/Red	7-1/8" (181.0 mm)	20 - 30 AWG Solid (0.50 mm ² - 0.14 mm ²), 22 - 32 AWG Stranded (0.34 mm ² - 0.05 mm ²)	6-32 and 8-32	5.1 oz. (145 g)

Dual NM Cable Stripper/Cutter

Additional Features:

- 12/2, and 14/2 stripping slots quickly remove outer jacket of Type NM-B nonmetallic-sheathed cable
- Stripping holes easily remove insulation on 12 and 14 AWG solid wire
- Precision shear-type blades for square, clean cuts on solid copper wire
- Narrow nose fits into tight places



SOLID
12 - 14 AWG



K1412

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type	Screw Shearing	Weight
K1412	Yellow/White	7-3/4" (196.9 mm)	12 and 14 AWG Solid (2.5 mm ² and 1.5 mm ²)	NM-B Cable 12/2 and 14/2	6-32 & 8-32	6.6 oz. (187 g)





Klein-Kurve™ Wire Strippers/Cutters

Dual NMD-90 Cable Stripper/Cutter

Additional Features:

- Quickly removes outer jacket of Canadian NMD-90 Romex® Cable
- Strips, cuts, and loops 12 & 14 AWG solid wires
- Strips, cuts, and loops 14 & 16 AWG stranded wires
- Cleanly shears 6-32 and 8-32 screws



K1412CAN



Romex® is a registered trademark of Southwire Company.

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type	Screw Shearing	Weight
K1412CAN	Yellow/White	7-3/4" (196.9 mm)	12 and 14 AWG Solid (2.5 mm ² and 1.5 mm ²), 14 and 16 AWG Stranded (1.5 mm ² and 1.0 mm ²)	NMD-90 Cable 12/2 & 14/2	6-32 & 8-32	6.6 oz. (187 g)

Textured handles provide a firm, comfortable grip

Spring loaded for self-opening action

Black-oxide finish resists corrosion

Easy-to-read wire gauge markings on both sides for stripping in either direction

Wire Strippers/Cutters

Wire looping and bending holes

Precision-ground stripping holes for easy removal of insulation



Wire Strippers/Cutters

Additional Features:

- Compact, lightweight wire-stripping and cutting tools
- Narrow nose fits into tight places
- Hardened steel with precision ground stripping holes
- Do NOT use for cutting steel wire or screws



11045

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight
11045	Yellow	6-1/4" (158.8 mm)	10 - 18 AWG Solid (4.0 mm ² - 0.75 mm ²)	4.3 oz. (122 g)
11046	Red	6-1/4" (158.8 mm)	16 - 26 AWG Stranded (1.0 mm ² - 0.14 mm ²)	4.3 oz. (122 g)
11047	Yellow	6-1/4" (158.8 mm)	22 - 30 AWG Solid (0.34 mm ² - 0.05 mm ²)	4.3 oz. (122 g)
11049	Red	6-1/4" (158.8 mm)	8 - 16 AWG Stranded (6 mm ² - 1.0 mm ²)	4.3 oz. (122 g)



Wire Strippers/Cutters

Dual-Wire Stripper/Cutter

Additional Features:

- Strips two wires in a single motion
- Paired stripping holes for 14 and 12 AWG solid wire
- One stripping hole for 10 AWG solid wire
- Shear-type cutting blades for square, clean cuts
- Narrow nose fits into tight places
- Hardened steel with precision ground stripping holes
- Do not use for cutting steel wire or screws



SOLID
10, 12, 14 AWG



11048

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight
11048	Yellow	6-1/4" (158.8 mm)	10, 12, 14 AWG Solid (4.0 mm ² , 2.5 mm ² , 1.5 mm ²)	4.3 oz. (122 g)

Wire Strippers/Cutters

- Strips six standard wire sizes without nicking wire
- Scissors action of 1/2" (13 mm) wide cutter makes clean cuts with little effort
- Serrated nose jaws to bend, shape or pull wire; holes for looping wire ends
- Spring-loaded for self-opening action
- Comfortable, plastic-covered handles

SOLID
10 - 20 AWG

STRANDED
12 - 22 AWG



1011

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight
1011M	Blue	6-1/8" (155.6 mm)	0.15 to 4.0 mm ² Stranded Wire	3.7 oz. (104 g)
1011	Blue	6-1/8" (155.6 mm)	10 - 20 AWG Solid (4.0 mm ² - 0.50 mm ²), 12 - 22 AWG stranded (2.5 mm ² - 0.34 mm ²)	3.7 oz. (104 g)

Adjustable Wire Strippers/Cutters - Solid and Stranded Wire

- A handy, light, compact tool for stripping insulation
- Convenient hole for looping or bending wire
- Black-oxide finish with plastic-dipped handles
- Cuts, strips, and loops 12-26 solid and stranded wire
- Adjustable slide stop with set screw for repeat stripping work

SOLID
12 - 26 AWG

STRANDED
12 - 26 AWG



1004

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Hold-Open Spring	Weight
1004	Yellow	5" (127.0 mm)	12 - 26 AWG Solid and Stranded (2.5 mm ² - 0.14 mm ²)	Yes	Yes
1003	Yellow	5" (127.0 mm)	12 - 26 AWG Solid and Stranded (2.5 mm ² - 0.14 mm ²)	No	2.2 oz. (64 g)

Adjustable Wire Stripper/Cutter - Solid and Stranded Wire

- Simply dial desired wire size for fast, easy stripping
- Adjustable tool makes short work of cutting and stripping operations
- Finely honed nose cutter easily gets into tight areas
- Wire gauge dial sets stripping dies to proper size, helps prevent nicked wire
- Black-oxide finish with plastic-dipped handles
- Spring-loaded design - tool opens automatically after each action

SOLID
12 - 24 AWG

STRANDED
12 - 24 AWG



74007

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight
74007	Yellow	5-1/8" (130.2 mm)	12 - 24 AWG Solid and Stranded (2.5 mm ² - 0.25 mm ²)	2.4 oz. (68 g)



Wire Strippers/Cutters

Katapult™ Wire Stripper/Cutters KATAPULT™

- Quick and easy wire stripping and cutting
- Compound action wire stripping: grip and strip via single action squeezing motion
- Precision machined stripping holes easily remove jacket insulation without damaging the wire
- Removes up to 1" (24 mm) in length of the insulation layer (jacket layer) in a single step
- Tension loaded wire-grip gently holds the cable in place while retaining the cable geometry
- Recoil spring design returns tool to ready position upon cycle completion
- Cast alloy chassis with heavy-duty Ecoat finish for corrosion resistance and durability
- Additional precision machined steel cutting blades available



11063W

Cat. No.	Handle Color	Overall Length	Strips	Weight
11063W	Blue/Black	6-19/32" (167.5 mm)	8 - 24 AWG solid (6.0 mm ² - 0.34 mm ²), 10-22 AWG stranded (6.0 mm ² - 0.34 mm ²)	12.0 oz. (340 g)

Cat. No.	Application	Weight
Replacement Blades Sets		
VDV110-046	RG6 Coaxial Cable	0.16 oz. (4.5 g)
11082	10 AWG Max Wire	0.16 oz. (4.5 g)
11073	8 - 22 AWG ((6.0 mm ² - 0.34 mm ²)	0.01 lbs. (0.005 kg)
11074	16 - 26 AWG ((1.0 mm ² - 0.14 mm ²)	0.01 lbs. (0.005 kg)
Wire Stop/Gauge		
11081	Adjustable Wire Stop	0.16 oz. (4.5 g)

Self-Adjusting Wire Stripper/Cutter

- Strips 10-20 AWG solid, 12-22 AWG stranded, and 12/2 & 14/2 Romex® wire
- Adjustable stopper to control the length of the core strip
- Convenient wire cutter in handle
- Grooved grips are designed for added comfort



11061

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight
11061	Blue/Black	8-1/4" (209.6 mm)	10 - 20 AWG Solid (4.0 mm ² - 0.50 mm ²), 12 - 22 AWG stranded (2.5 mm ² - 0.34 mm ²), 12/2 and 14/2 Romex®	12.6 oz. (358 g)

Romex® is a registered trademark of Southwire Company.

NM Cable Ripper

- Easy-to-use cable ripper
- Slit the outer jacket of Romex® cable (all sizes) and other nonmetallic (type NM) sheathed cable
- Measure conductor wire gauge



74017

Cat. No.	Overall Length	Slits	Measures Wire Gauge	Weight
74017	4" (101.6 mm)	All Sizes of Romex® and NM	8 - 14 AWG (6 mm ² - 1 mm ²)	1.3 oz. (37 g)

Romex® is a registered trademark of Southwire Company.



Combination Wire-Stripping and Crimping Tools

Multi-Purpose 6-in-1 Tool

- Cleanly shears bolts
- Easily cuts and strips wire
- Measures stud sizes
- Gauges wire sizes
- Crimps insulated terminals
- Comfortable, plastic-covered handles

SOLID
8 - 22 AWG

STRANDED
10 - 26 AWG



1000



Cat. No.	Handle Color	Overall Length	Strips and Cuts	Bolt Size	Weight
1000	Red	7-3/4" (196.9 mm)	8 - 22 AWG Solid (6.0 mm ² - 0.34 mm ²), 10 - 26 AWG Stranded (4.0 mm ² - 1.0 mm ²)	4-40, 6-32, 8-32, 10-24, 10-32	7.0 oz. (198 g)

Multi-Purpose Electrician's Tool

- Two wire cutters—one at tip, the other halfway back near stripping holes—double the utility of this tool
- Color-coded crimping dies for 10-22 AWG insulated and non-insulated terminals
- Cleanly shears bolts
- Pivot nut adjusts tension
- Wire-looping holes near tip
- Full-sized, plastic-covered cushioned handles for comfort

SOLID
8 - 22 AWG

STRANDED
10 - 26 AWG



1001



Cat. No.	Handle Color	Overall Length	Strips and Cuts	Bolt Size	Weight
1001	Red	8-1/2" (215.9 mm)	8 - 22 AWG Solid (6.0 mm ² - 0.34 mm ²), 10 - 26 AWG Stranded (4.0 mm ² - 1.0 mm ²)	4-40, 6-32, 8-32, 10-24, 10-32	7.5 oz. (213 g)

Multi-Purpose Long-Nose Tool

- Easily cuts and strips wire
- Narrow, serrated pliers nose to pull, loop, and bend wire
- Long, curved cutting blade
- Cutters and strippers are in front of the pivot for maximum ease-of-use in reaching into tight places
- Crimps insulated and non-insulated terminals and 7 to 8 mm ignition terminals
- Cleanly shears bolts
- Plastic-covered cushioned handles for comfort

SOLID
10 - 20 AWG

STRANDED
12 - 22 AWG



1010




Cat. No.	Handle Color	Overall Length	Strips and Cuts	Bolt Size	Connectors	Weight
1010	Blue	8-1/4" (209.6 mm)	10 - 20 AWG, 12 - 22 AWG	4-40, 5-40, 6-32, 8-32, 10-32, 10-24	10 - 22 Gauge	6.9 oz. (196 g)

Crimping Tools

Crimping/Cutting Tools - Non-Insulated/Insulated Terminals

- Crimping die marked for insulated and non-insulated solderless terminals and connectors
- Tapered nose design for working in confined spaces
- Specially hardened wire cutter in nose
- Hot-riveted joint for smooth action and no handle wobble



1005



Cat. No.	Overall Length	Handle Finish	Handle Color	Crimps	Weight
1005	9-3/4" (247.7 mm)	Plastic-dipped	Red	10 - 22 AWG (4.0 mm ² - 0.34 mm ²)	12.8 oz. (363 g)
Journeyman Series – Dual-material handles					
J1005	9-3/4" (247.7 mm)	Journeyman	Red/Black	10 - 22 AWG (4.0 mm ² - 0.34 mm ²)	13.4 oz. (381 g)



Crimping Tools

Crimping/Cutting Tool - Non-Insulated Terminals

- Designed for crimping non-insulated solderless terminals and connectors
- Specially hardened wire cutter in nose
- Tapered nose for working in confined spaces
- Hot-riveted joint for smooth action and no handle wobble



1006

Cat. No.	Handle Color	Overall Length	Crimps	Weight
1006	Black	9-3/4" (247.7 mm)	10 - 22 AWG (4.0 mm ² - 0.34 mm ²)	13.6 oz. (386 g)

Large Crimp Tool - Compound-Action

- Crimps #6-4/0 AWG battery lugs and terminals
- Ultra-comfortable hand grips for easy use
- All-in-one, integral crimp nest. No removable parts or rotating dies
- High-leverage handles and compound-action mechanism for superior mechanical advantage
- Adjustment screw allows user to control crimp depth



2006

Cat. No.	Handle Color	Overall Length	Crimps	Weight
2006	Red	19-1/2" (495.3 mm)	#6 - 4/0 AWG battery lugs and terminals	3.8 lbs. (1.72 kg)

Ratcheting Crimpers

Ratcheting Crimpers - Insulated Terminals

- Cat. No. T1715 full cycle ratcheting crimper crimps insulated terminals in wire sizes 22-16 (front cavity), 16-14 (middle cavity), and 12-10 (rear cavity)
- Cat. No. T1710 compound-action tool crimps 10-22 AWG insulated terminals to meet or exceed MIL-SPEC pull-out tests
- Cat. No. T1710 features special locator to quickly position terminal to double crimp
- Built-in ratchet with safety release assures uniform crimps every time
- Compound lever-action of narrow span handles puts more crimping power into each squeeze
- Comfort-grip plastic handles



T1715



T1710

Cat. No.	Handle Color	Overall Length	Crimps	Weight
T1715	Black	9" (228.6 mm)	22-16/16-14/ 12-10	1.1 lbs. (0.50 kg)
T1710	Black	9" (228.6 mm)	10 - 22 AWG	1.1 lbs. (0.50 kg)

