

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192030078

Status:

Active

Overview:

ring_tongue_spade_terminals

Description:

Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

Type

Ring and Spade Terminals

19203

1200° F (649° C)

Yes

N/A

ring_tongue_spade_terminals

Krimptite™, Temp-Terms

Ring

Physical

Barrel Type

Insulation

Material - Plating Mating

Packaging Type

Stud Size

Wire Size AWG

Wire Size mm²

Closed

None

Tin

Adhesive Tape on Reel

6 (M3.5)

14, 16

1.00 - 2.50

Material Info

Old Part Number

BB-U-123-06T

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011

BBCD10104



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19203Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Mini-Mac™	0638853900
Applicator, Air Feed Mylar Tape	
ATP Perishable	0190270068
Tool Kit used in ATP presses that process product on tape	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0078](#)