

Video Patchcords



Switchcraft's new broadcast series video patch cords are available in eight base ten colors. The unique lowloss 75 Ohm rated cable is ideal for patching in both SD or HD applications. The outer jacket is made very flexible which allows for a low retract memory.

Features and Benefits

- Rugged nickel-plated handles knurled for positive finger grip.
- Flexible black “boot” placed on all cable colors for more positive grip and cable strain relief.
- Overall flexible jacket for easy coil and low retract memory.

Broadcast Series

Video Patchcords: Standard WECO and midsize

Part Numbering System



Standard WECO (.090 Center Pin)

VP

Video
Patch

Length
(Feet)

Cable
Color



Midsize Mini-WECO (0.48 Center Pin)

VMP

Video
MidSize
Patch

Length
(Feet)

Cable
Color

Colors	Color Code	Standard Foot Lengths
		1'
Black	BK	2'
Red	R	3'
Orange	O	4'
Yellow	Y	5'
Green	GN	6'
Blue	BL	7'
Purple	P	8'
Gray	GY	9'
		10'

Custom lengths are available by request.
1 meter is equal to 3.28 feet.

Plug Specifications:

Plug Barrel:

- Nickel plated copper alloy.
- 0.375 inches outside diameter, for standard size video plug.
- 0.298 inches outside diameter, for mid size video plug.

Handle:

- Nickel plated copper alloy.

Contact Pin:

- Gold-plated copper alloy.
- .090 inches diameter, for std. video plug.
- .048 inches diameter, for midsize video plug.

Boot:

- Black Thermoplastic.