

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100025](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Pro-Yellow 60W Screw Mount Machine Light, with Molded 18/2 SJTOW Cord Type, Overall Cord Length 3.04m (10.0')



Series image - Reference only

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 1-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Pro-Yellow
Type	Wide Area Lamps
UPC	78678808531

Physical	
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	No
Guard Type	N/A
Height	N/A
Length	727.20mm (28.630")
Material - Globe	Tempered Glass
Material - Guard	Nylon
Mounting Style	Magnet
Packaging Type	Carton
Socket Construction	N/A

Electrical	
Bulb Type	Incandescent
Cord Type - Primary	18/2 SJTOW
Lamp Type	A19
Lamp Wattage - Maximum	60W
Lumens	600
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120V AC

Material Info	
Engineering Number	8530P

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130110 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION