




Euromas-Aluminium / F05 enclosures

Robust aluminium enclosure with protection class IP 66

- 43 sizes
- Listing under UL file no. E 196 706
- Versions with silicone lid seal with higher temperature resistance (approx. 130°C)
- Types with crystal-clear lid on request
- SWB types available on request for saltwater-proof applications or for applications requiring higher levels of anti-corrosion protection
- EMC set on request for increasing electromagnetic shielding levels
- Terminals and mounting on request
- Types made of Vestamid or aluminium with F05 insertion opening



Colour	Silver grey, similar to RAL 7001; special colours on request. V 215: black, similar to RAL 9005
Protection class	IP 66/DIN EN 60529, higher protection class on request. V 215: IP 65/DIN EN 60529
Enclosure material	G Al Si 12, PU foamed seal; V215: Vestamid, CR seal; for details see Technical Information





Maximum insertion with Phoenix modular terminals

	MBK 2.5	MBK 3	MBK 5	UK 3 N	UK 5 N	UK 10 N
DIN rail TS 15	x	x	x			
DIN rail TS 32				x	x	x
DIN rail TS 35				x	x	x
Bridgeable		x	x	x	x	x
End-angle piece	2	2	2	2	2	2
End plate	-	1	1	1	1	1
Conductor cross-section (mm²) fine-strand	1.5	2.5	4	2.5	4	10
Conductor cross-section (mm²) single-wire	2.5	4	4	4	6	16
Nominal voltage (V)	500	500	500	750	750	800
Current-carrying capacity (A)	26	32	34	34	34	76
Terminal width (mm)	5.2	5.2	6.2	5.2	6.2	10.2

Model	Number per DIN rail					
A 100						
A 101	4					
A 102	11					
A 103	20					
A 104	14					
A 105	6	6	6			
A 106	24	24				
A 110	16	16	12			
A 114	30	30	25			
A 115	26	26	22			
A 116	11	11	9			
A 117	40	40	34			
A 118	22	22	18			
A 119				12	10	6
A 120				12	10	6
A 121				15	13	8
A 122				31	26	15
A 123				31	26	15
A 124				58	48	29
A 125				19	16	9
A 126				27	22	13
A 127				23	19	11
A 130				38	32	19
A 131				42	35	21
A 135				57	48	29
A 138				96	80	49
A 140				27	22	13
A 145				32	27	16
A 150				27	22	13
A 155				42	35	21
A 160				52	43	26
A 165				52	43	26
A 168				65	55	33
A 169				103	87	53
A 170				65	55	33

	MBK 2.5	MBK 3	MBK 5	UK 3 N	UK 5 N	UK 10 N
Model	Number per DIN rail					
A 175				65	55	33
A 180				65	55	33
A 185				65	55	33
A 190				65	55	33
A 195				69	58	35
A 196				103	87	53
A 197				103	87	53
A 198				103	87	53

Maximum insertion with Weidmüller modular terminals

	AKZ 1.5	AKZ 2.5	AKZ 4	SAK 2.5	SAK 4
DIN rail TS 15	x	x	x		
DIN rail TS 32				x	x
DIN rail TS 35					
Bridgeable	x	x	x	x	x
End-angle piece	2	2	2	2	2
End plate	1	1	1	1	1
Conductor cross-section (mm ²) fine-strand	1.5	2.5	4	2.5	4
Conductor cross-section (mm ²) single-wire	2.5	4	6	4	10
Nominal voltage (V)	400	250	500	800	800
Current-carrying capacity (A)	17.5	24	32	24	32
Terminal width (mm)	5	5	6	6	6.5

Model	Number per DIN rail				
A 100		1 x MK3/4 terminal block			
A 101		1 x BK4 terminal block			
A 102		1 x BK6 terminal block			
A 103		1 x BK12 terminal block			
A 104		1 x BK12 terminal block			
A 105	6	6	4		
A 106		1 x BK12 terminal block			
A 110	15	15	12		
A 114	30	30	25		
A 115	25	25	20		
A 116	10	10	8		
A 117	40	40	33		
A 118	22	22	18		
A 119				10	9
A 120				10	9
A 121				13	12
A 122				26	24
A 123				26	24
A 124				50	46
A 125				16	15



Maximum insertion with Weidmüller modular terminals

	AKZ 1.5	AKZ 2.5	AKZ 4	SAK 2.5	SAK 4
Modell	Number per DIN rail				
A 126				23	21
A 127				20	18
A 130				33	30
A 131				36	33
A 135				50	46
A 138				83	77
A 140				23	21
A 145				28	26
A 150				23	21
A 155				36	34
A 160				45	41
A 165				45	41
A 168				56	52
A 169				90	83
A 170				56	52
A 175				56	52
A 180				56	52
A 185				56	52
A 190				56	52
A 195				60	55
A 196				90	83
A 197				90	83
A 198				90	83

Euromas-Aluminium



Euromas enclosure, aluminium

Model	Order no.	A	B	C	a1	a2	b1	b2	b3	c1	c2
A 100	01100000	50	45	30	44	30	39	25		6	25
A 101	01101000	58	64	34	50,5	34	56,8	32		9	28,5
A 101 G	01101500*	58	64	34	50,5	34	56,8	32		9	28,5
A 102	01102000	98	64	34	90,5	74	56,8	32		9	28,5
A 102 G	01102500*	98	64	34	90,5	74	56,8	32		9	28,5
A 103	01103000	150	64	34	142,5	126	56,8	32		9	28,5
A 104	01104000	115	64	34,5	107,5	90,6	56,5	31,6		9	29
A 105	01105000	75	80	57	65,5	50,4	70,5	47,4		15	51
A 105 G	01105500*	75	80	57	65,5	50,4	70,5	47,4		15	51
A 106	01106000	186	64	34,5	178	161,1	56,5	31,6		9	29
A 110	01110000	125	80	57	115,5	100,4	70,5	47,4		15	51
A 110 G	01110500*	125	80	57	115,5	100,4	70,5	47,4		15	51
A 114	01114000	200	100	81	190	172	90	52		20	74
A 115	01115000	175	80	57	165,5	150,4	70,5	47,4		15	51
A 115 G	01115500*	175	80	57	165,5	150,4	70,5	47,4		15	51
A 116	01116000	100	100	81	90	72	90	52		20	74
A 117	01117000	250	80	52	240,5	225,4	70,5	47,4		12	45
A 118	01118000	160	100	81	150	132	90	52		20	74
A 119	01119000	122	120	81	111	88	109	64		20	72
A 120	01120000	122	120	91	111	89,1	109	64		30	82
A 121	01121000	140	140	91	129	101	129	74		30	82
A 122	01122000	220	120	81	209	186	109	64		20	72
A 123	01123000	220	120	91	209	186	109	64		30	82
A 124	01124000	360	120	81	349	326	109	64		20	72
A 125	01125000	160	160	91	148,6	117,6	149	88		20	82
A 126	01126000	200	140	91	189	161	129	74		30	82
A 127	01127000	180	180	101	169	138	169	108		30	92
A 130	01130000	260	160	91	248,6	217,6	149	88		20	91
A 131	01131000	280	180	101	269	238	169	108		30	92
A 135	01135000	360	160	91	348,6	317,6	149	88		20	82
A 138	01138000	560	160	91	548,5	517,5	149	88	113	20	82
A 140	01140000	200	230	111	189	157	219	157		20	102
A 145	01145000	230	100	111	218	158	88	58		20	101
A 150	01150000	200	230	180	190	158	220	158		20	170
A 155	01155000	280	230	111	268	237	218	157		20	102
A 160	01160000	330	230	111	318	286,5	217,5	156,5		20	102
A 165	01165000	330	230	181	316,5	285,5	216,5	155,5		20	170
A 168	01168000	400	230	111	387	357	217	157		20	102
A 169	01169000	600	230	111	586	558	216	158	188	20	100
A 170	01170000	400	230	225	384,5	354,5	214,5	155		20	214,5
A 175	01175000	400	310	111	392	359,5	301	239		20	101



Euromas-Aluminium

Euromas enclosure, aluminium


Model	Order no.	A	B	C	a1	a2	b1	b2	b3	c1	c2
A 180	01180000	400	310	141	386,5	358	296,5	238,5		20	129,5
A 185	01185000	400	310	181	390	358,5	299	238		20	169,5
A 190	01190000	400	310	227	388,5	360,5	297,5	240		20	216
A 195	01195000	420	240	209,5	403,5	372,8	225	164		20	200,5
A 196	01196000	600	310	111	586	558	296	238	268	20	99,5
A 197	01197000	600	310	181	584	556	294	236	266	20	169,5
A 198	01198000	600	600	202,5	583	547	583	547	547	40	189

Scope of delivery: Lid and base, lid screws made of V2A, earthing screw

Note: * = Available on request. Accessories: See following pages.

A 198: Because of the wall fixing drill holes inside the sealed section of the enclosure, expert sealing of the wall fixing is necessary to attain protection class IP 66.

G = design with transparent lid (PC)



Euromas-Aluminium



Euromas enclosure, aluminium, with silicone lid seal

Model	Order no.	A	B	C	a1	a2	b1	b2	b3	c1	c2
A 100 SIL	01100010	50	45	30	44	30	39	25		6	25
A 101 SIL	01101010	58	64	34	50,5	34	56,8	32		9	28,5
A 102 SIL	01102010	98	64	34	90,5	74	56,8	32		9	28,5
A 103 SIL	01103010	150	64	34	142,5	126	56,8	32		9	28,5
A 104 SIL	01104010	115	64	34,5	107,5	90,6	56,5	31,6		9	29
A 105 SIL	01105010	75	80	57	65,5	50,4	70,5	47,4		15	51
A 106 SIL	01106010	186	64	34,5	178	161,1	56,5	31,6		9	29
A 110 SIL	01110011	125	80	57	115,5	100,4	70,5	47,4		15	51
A 114 SIL	01114010	200	100	81	190	172	90	52		20	74
A 115 SIL	01115010	175	80	57	165,5	150,4	70,5	47,4		15	51
A 116 SIL	01116010	100	100	81	90	72	90	52		20	74
A 117 SIL	01117010	250	80	52	240,5	225,4	70,5	47,4		12	45
A 118 SIL	01118010	160	100	81	150	132	90	52		20	74
A 119 SIL	01119010	122	120	81	111	88	109	64		20	72
A 120 SIL	01120010	122	120	91	111	89,1	109	64		30	82
A 121 SIL	01121010	140	140	91	129	101	129	74		30	82
A 122 SIL	01122010	220	120	81	209	186	109	64		20	72
A 123 SIL	01123011	220	120	91	209	186	109	64		30	82
A 124 SIL	01124010	360	120	81	349	326	109	64		20	72
A 125 SIL	01125011	160	160	91	148,6	117,6	149	88		20	82
A 126 SIL	01126010	200	140	91	189	161	129	74		30	82
A 127 SIL	01127010	180	180	101	169	138	169	108		30	92
A 130 SIL	01130011	260	160	91	248,6	217,6	149	88		20	91
A 131 SIL	01131010	280	180	101	269	238	169	108		30	92
A 135 SIL	01135011	360	160	91	348,6	317,6	149	88		20	82
A 138 SIL	01138010	560	160	91	548,5	517,5	149	88	113	20	82
A 140 SIL	01140010	200	230	111	189	157	219	157		20	102
A 145 SIL	01145010	230	100	111	218	158	88	58		20	101
A 150 SIL	01150010	200	230	180	190	158	220	158		20	170
A 155 SIL	01155010	280	230	111	268	237	218	157		20	102
A 160 SIL	01160010	330	230	111	318	286,5	217,5	156,5		20	102
A 165 SIL	01165010	330	230	181	316,5	285,5	216,5	155,5		20	170
A 168 SIL	01168010	400	230	111	387	357	217	157		20	102
A 169 SIL	01169010	600	230	111	586	558	216	158	188	20	100
A 170 SIL	01170010	400	230	225	384,5	354,5	214,5	155		20	214,5
A 175 SIL	01175010	400	310	111	392	359,5	301	239		20	101
A 180 SIL	01180010	400	310	141	386,5	358	296,5	238,5		20	129,5
A 185 SIL	01185010	400	310	181	390	358,5	299	238		20	169,5



Euromas-Aluminium


Euromas enclosure, aluminium

Model	Order no.	A	B	C	a1	a2	b1	b2	b3	c1	c2
A 195 SIL	01195010	420	240	209,5	403,5	372,8	225	164		20	200,5
A 196 SIL	01196010	600	310	111	586	558	296	238	268	20	99,5
A 197 SIL	01197010	600	310	181	584	556	294	236	266	20	169,5
A 198 SIL	01198010	600	600	202,5	583	547	583	547	547	40	189

Scope of delivery: Lid and base, lid screws made of V2A, earthing screw

Note: For accessories, see following pages

A 198: Because of the wall fitting drill holes inside the sealed lip, expert sealing of the wall fitting is required to achieve protection class IP 66.



Euromas accessories

Mounting panels, galvanised sheet steel

Model	Order no.	Note
M	21001100	For A 105, PK 105
M	21001200	For A 110, PK 110
M	21001202	For A 114
M	21001300	For A 115, PK 115
M	21001310	For A 116
M	21001320	For A 118
M	21001600	For A 119-120, P 332
M	21001610	For A 121
M	21001500	For A 122-123, P 331
M	21001550	For A 124
M	21001700	For A 125, P 330
M	21001710	For A 126
M	21001720	For A 127
M	21001800	For A 130, P 333
M	21001810	For A 131
M	21001900	For A 135, P 334
M	21002000	For A 138, P 345
M	21002100	For A 140, A 150
M	21002110	For A 145
M	21002120	For A 155
M	21002200	For A 160-165
M	21002400	For A 168, A 170
M	21002410	For A 169
M	21002420	For A 175-190
M	21002500	For A 195
M	21002510	For A 196-197
M	21002520	For A 198

Scope of delivery: 1 mounting panel



Euromas accessories



Capstan-headed screws, sealable

Model	Order no.	Note
KP	21007915	For A 100-118
KP	21007955	For A 119, A 122, A 124-125, A 130, A 135-190, A 196-197
KP	21007995	For A 120-121, A 123, A 126-127, A 131, P 331-332, P 337, P 341-342, P 335
KP	21007975	For A 195, P 330, P 333-336, P 339, P 345

Scope of delivery: 2 pieces



Allen cheese-head screw for lid

Model	Order no.	Note
IS	21007910	For A 100
IS	21007920	For A 101-118
IS	21007950	For A 119, A 122, A 124-125, A 130, A 135, A 140-168, A 170-190
IS	21007990	For A 120-121, A 123, A 126-127, A 131, P 331-332, P 337, P 341, P 3412, P 355
IS	21007960	For A 138, A 169, A 196-197
IS	21007970	For A 195, P 330, P 333-336, P 339
IS	21008010	For A 198

Scope of delivery: 1 set, suitable for one enclosure

Euromas accessories

Earthing bars with fitted terminal clamps

Model	Order no.	Note
E	21004600	For A 119-120, P 332
E	21004650	For A 121
E	21004700	For A 122-123, P 331
E	21005000	For A 124, A 135, P 334, P 339
E	21004800	For A 125, P 330
E	21004850	For A 126, A 140, A 150
E	21004860	For A 127
E	21004900	For A 130, P 333, P 337-338
E	21004950	For A 131
E	21005100	For A 138, P 345
E	21005250	For A 155
E	21005300	For A 160-165
E	21005400	For A 168, A 170-190, P 340-341, P 3412, P 355
E	21005500	For A 169, P 342
E	21005600	For A 195
E	21005650	For A 196-197

Scope of delivery: 1 earthing bar



Wall brackets, screw-on at rear

Model	Order no.	Note
WL	21004250	For A 114, A 116, A 118, P 305-322, P 324-329
WL	21004300	For A 119-198, P 330-355

Scope of delivery: 4 pieces



DIN rails DIN EN 60715 TH 15

Model	Order no.	Note
TS 15	21002650	For A 101
TS 15	21002600	For A 102
TS 15	21002700	For A 103
TS 15	21002800	For A 105, P 305, P 326, PK 105
TS 15	24003300	For A 106, P 319, P 329
TS 15	21002900	For A 110, PK 110
TS 15	21002950	For A 114
TS 15	21003000	For A 115, PK 115
TS 15	21003050	For A 116
TS 15	21003100	For A 117
TS 15	21003150	For A 118, P 316
TS 15	21003205	For A 119-120, P 332
TS 15	21003310	For A 122-123
TS 15	21003505	For A 130, P 333
TS 15	21004210	For A 195

Scope of delivery: 1 DIN rail



Euromas accessories



DIN rails DIN EN 60715 G 32

Model	Order no.	Note
TS 32	21002960	For A 114
TS 32	21003160	For A 118
TS 32	21003200	For A 119-120, P 332
TS 32	21003250	For A 121
TS 32	21003300	For A 122-123, P 331
TS 32	21003340	For A 124, A 135, P 334, P 339
TS 32	21003400	For A 125, P 330
TS 32	21003450	For A 126
TS 32	21003470	For A 127
TS 32	21003500	For A 130, P 333
TS 32	21003550	For A 131
TS 32	21003700	For A 138, P 345
TS 32	21003800	For A 140, A 150
TS 32	21003850	For A 145
TS 32	21003870	For A 155
TS 32	21003900	For A 160-165
TS 32	21004100	For A 168, A 170-190, P 340-341, P 3412, P 355
TS 32	21004150	For A 169, A 196-197, P 342
TS 32	21004200	For A 195
TS 32	21004170	For A 198

Scope of delivery: 1 DIN rail



DIN rails DIN EN 60715 TH 35

Model	Order no.	Note
TS 35	21002920	For A 110
TS 35	21003210	For A 119-120, P 332
TS 35	21003270	For A 121
TS 35	21003320	For A 122-123, P 331
TS 35	21003350	For A 124, A 135, P 334, P 339
TS 35	21003410	For A 125, P 330
TS 32	21003470	For A 127
TS 35	21003480	For A 127
TS 35	21003510	For A 130, P 333
TS 35	21003560	For A 131
TS 35	21003710	For A 138, P 345
TS 35	21003810	For A 140, A 150

Euromas accessories

DIN rails DIN EN 60715 TH 35

Model	Order no.	Note
TS 35	21003860	For A 145
TS 35	21003880	For A 155
TS 35	21003910	For A 160-165
TS 35	21004110	For A 168, A 170-190, P 340-341, P 3412, P 355
TS 35	21004160	For A 169, A 196-197, P 342
TS 35	21004205	For A 195
TS 35	21004180	For A 198

Scope of delivery: 1 DIN rail



Hinge set, diecast

Model	Order no.
SCHD	21007800

Scope of delivery: 1 hinge set

Note: Mechanical processing is required for mounting hinges.



Euromas enclosures with F05 insertion



Euromas, aluminium, with F05 opening, IP 66 / DIN EN 60529

Model	Order no.	A	B	C
A 110 F05	01110800	125	80	57
A 110 F05 Ex	01110600	125	80	57

Scope of delivery: Base, lid, for EX design additional EX type plate, earthing connection M 4 internal and external

Note: For the A 110 F05 EX, a component check was carried out according to directive 94/9/EC. EC type examination certificate PTB 04 ATEX 1116 U.

Explosion protection:


- EX II 2G EExe II
- EX II 2D IP 66

Further information on A 110 F05:

1. Cable and wire inlets and blanking plugs acc. to DIN 46320 and 46255 with separate test certificate and separately tested elastomer seal.
2. Operating temperatures for the adjusting axis sealing rings:
 - Round sealing ring 9.0x1.5 – NBR 70: -30°C ... +100°C
 - Round sealing ring 9.0x1.5 – VMQ 70 (silicone): -55°C ... +155°C

Important: As the installation of the adjusting axis including the adjusting axis seal only takes place during complete assembly of the enclosure, the manufacturer of the complete unit is responsible for ensuring compliance with protection class IP 65 acc. to DIN EN 60529 for this sealed point! The enclosure manufacturer cannot accept any warranty in respect of this.

EX cable glands as accessories.



Euromas enclosures with F05 insertion


Euromas, Vestamid, with F05 opening, black, IP 65

Model	Order no.	A	B	C	Note
V 215 F05-PST	02215612	120	80	55	Euromas Vestamid enclosure with F05 insertion opening, with PST cut-out
V 215 F05-FG-PST	02215622	120	80	55	Euromas Vestamid enclosure with F05 insertion opening, with PST cut-out and window
V 215 F05-ZR	02215613	120	80	55	Euromas Vestamid enclosure with F05 insertion opening, with centring ring
V 215 F05-FG-ZR	02215623	120	80	55	Euromas Vestamid enclosure with F05 insertion opening, window and centring ring

Scope of delivery: Base, lid

Note: Please order Pg 13 plug-in cable gland for PST cut-out separately (order no. 12060407).
Design with crystal-clear lid (PC) and in enclosure material PC-light grey, similar to RAL 7035, available on request.

Important: As the installation of the adjusting axis including the adjusting axis seal only takes place during complete assembly of the enclosure, the manufacturer of the complete unit is responsible for ensuring compliance with protection class IP 65 acc. to DIN EN 60529 for this sealed point!
The enclosure manufacturer cannot accept any warranty in respect of this.



Z-2503224