

MODEL TL-4902



International size reference: 1/2AA, ER14252

TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



■ Nominal capacity @ 0.5 mA, to 2 V	1.2 Ah
■ Rated voltage	3.6 V
■ Maximum recommended continuous current	20 mA
■ Maximum 1 sec. pulse capability	50 mA
■ Weight	9.6 g (0.338 oz)
■ Volume	4 cc
■ Operating temperature range	-55 °C to +85 °C
■ U.L. Component Recognition, MH 12193	

***TADIRAN
LITHIUM
BATTERIES***



AVAILABLE TERMINATIONS

SUFFIX- /S STANDARD	15-4902-21000
SUFFIX- /T SOLDER TABS	15-4902-31000
SUFFIX- /P AXIAL PINS	15-4902-41000
SUFFIX- /PT2 RADIAL PINS	15-4902-36000
SUFFIX- /TP POLARIZED TABS	15-4902-52000
SUFFIX- /PT POLARIZED TABS	15-4902-53000



XOL - Extended Operating Life

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

ECN 1501174 Rev. C 01/06