

**Standard Barrel Copper Lug****T&B Catalog Number:**

53168

UPC Number:

78620987120

Status:

Active

Description:

Cast Copper One-Hole Heavy Duty Lug - Straight Standard Barrel - max 35KV, 1100/24 Wire, 1/2 Bolt Size, Tin Plated Blind End, Orange 107

Features

Electro Tin-Plated for Corrosion Resistance. Chamfered Barrels Provide Ease of Strand Entry and Inspection hole facilitates full insertion of the conductor.

Cable Area Clearly Identified on Lug.

General

Style	Heavy-Duty
Material	Cast Copper
Finish	Tin Plated
Wire Size	1100/24
Number of Studs	1
Stud Size (inches)	1/2
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Color	Orange
Die Code	107

Dimension Information

A (inches)	3 5/16
B (inches)	1 5/8
C (inches)	1 5/8
D (inches)	13/32
F (inches)	7/8

Specifications

Temperature Rating	105°C
Voltage Rating	600V to 35KV

Tooling

Connector & Tooling Chart Available on Website

Packaging

T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	38 lbs. per 100

Application Support

Overview Available on Website

Notes

Dimensions given for reference only. Dimensions
may vary up to +/- .030.

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com