




MATERIAL: BRASS

FINISH: ELECTRO-TIN PLATING

INSULATION: PVC

* MWID=MAXIMUM WIRE INSULATION DIAMETER

PART NUMBER	INS. COLOR	WIRE RANGE AWG MM ²	FITS MALE TAB SIZE	STOCK THICK.	"L" MAX.	"I" MAX.	"W" MAX.	"D" ±.01	"H" ±.01	"E" NOM.	MV
AA-2140	RED	22-18 0.25-1.3	.250x.032	.016	.88	.41	.30	.156	.103	.31	.0
BB-2141	BLUE	16-14 1.0-2.6	.250x.032	.016	.88	.41	.30	.156	.103	.31	.0
P-2142	YELLOW	14-12 1.65-4.2	.250x.032	.016	.88	.41	.30	.156	.103	.31	.0
C-2143	YELLOW	12-10 2.6-6.6	.250x.032	.018	1.00	.56	.30	.156	.110	.31	.2
AA-2190-032	RED	22-18 0.25-1.3	.205x.032	.016	.78	.41	.251	.125	.103	.25	.0
BB-2191-032	BLUE	16-14 1.0-2.6	.205x.032	.016	.78	.41	.251	.125	.103	.25	.0
AA-2190	RED	22-18 0.25-1.3	.205x.020	.016	.78	.41	.251	.125	.086	.25	.0
BB-2191	BLUE	16-14 1.0-2.6	.205x.020	.016	.78	.41	.251	.125	.086	.25	.0
AA-2137-032	RED	22-18 0.25-1.3	.187x.032	.016	.78	.41	.24	.125	.103	.25	.0
BB-2138-032	BLUE	16-14 1.0-2.6	.187x.032	.016	.78	.41	.24	.125	.103	.25	.0
P-2139-032	YELLOW	14-12 1.65-4.2	.187x.032	.016	.78	.41	.24	.125	.103	.25	.0
AA-2137	RED	22-18 0.25-1.3	.187x.020	.016	.78	.41	.24	.125	.086	.25	.0
BB-2138	BLUE	16-14 1.0-2.6	.187x.020	.016	.78	.41	.24	.125	.086	.25	.0
P-2136	YELLOW	14-12 1.65-4.2	.187x.020	.016	.78	.41	.24	.125	.086	.25	.0

REVISE ONLY ON CAD SYSTEM

TITLE

INSULKRIMP
QUICK DISCONNECT


CUSTOMER DRAWING

DRWG.	RCM
BY	

CHK'D. BY	
--------------	--

APP'D.
BY

SCALE	NO:NE
-------	-------



INC.
PINELLAS PARK, FLA. 34665 U.S.A.

PART NO.

SEE TABLE


FILE NAME
CD2901

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX-ETC INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SHEET NO	
----------	--

CD

DRWG. NO.



PARTS ON

PART NUMBERS ARE FOR
PIECE ,TO ORDER PARTS
ADD A "T" TO END OF PA

6

5

4

3

2