

38012 Hook-up/Lead - UL Type PV Wire

For more Information
please call

1-800-Belden1

**Description:**

12 AWG stranded (65x30) tinned copper conductors, XLPE insulation, sunlight resistant, photovoltaic wire.

Usage (Overall)**Suitable Applications:**

Interconnection wiring of grounded and ungrounded photovoltaic power systems as described in Section 690.31(A) of the 2008 NEC.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
1	12	65x30	TC - Tinned Copper

Total Number of Conductors:

1

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
XLPE - Cross Linked Polyethylene	0.063

Separator**Separator Material over Conductor:**

Paper tape

Overall Cable**Overall Nominal Diameter:**

0.219 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +90°C

UL Temperature Rating: 90°C Wet/Dry

Bulk Cable Weight: 36 lbs/1000 ft.

Max. Recommended Pulling Tension: 84.500 lbs.

Min. Bend Radius/Minor Axis: 2.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

UL Rating: 600V, 90C

UL Type: PV, USE-2, RHW-2

CSA Rating: 1000V, 90C

CSA Type: RW90

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 09/01/2009

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

38012 Hook-up/Lead - UL Type PV Wire

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: VW-1

CSA Flame Test: FT1

Suitability

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.500

Max. Operating Voltage - UL:

Voltage

600 V RMS

Max. Operating Voltage - Other:

Voltage Description

1000V RMS CSA

Max. Recommended Current:

Description Current

Single conductor in free air @ 30 ambient 40 amps

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
38012 0101000	1,000 FT	38.000 LB	BLACK		#12 STR XLPE BLK
38012 0105000	5,000 FT	190.000 LB	BLACK		#12 STR XLPE BLK

Revision Number: 0 Revision Date: 06-16-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[38012 0101000](#) [38012 0105000](#)