







Bereich für Presssitz
mit Übergabestiften
*area for press-fit
to interface pins*



A - A
2 : 1



Nr no	Artikel-Nr. part no.	LP-Dicke pcb-thickness	Kontaktlänge contact length	a±0,1
1	09 23 000 9950.00	3,0 ±0,4	20,0 ±0,3	11,75
2	09 23 000 9951.00	4,0 ±0,4	20,0 ±0,3	10,7
3	09 23 000 9952.00	1,6 ±0,4	17,0 ±0,3	9,9
		4,8 ±0,4	20,0 ±0,3	
4	09 23 000 9953.00	2,4 ±0,4	17,0 ±0,3	9,1
		5,6 ±0,4	20,0 ±0,3	
5	09 23 000 9954.00	3,2 ±0,4	17,0 ±0,3	8,3
		6,4 ±0,4	20,0 ±0,3	
6	09 23 000 9955.00	4,0 ±0,4	17,0 ±0,3	7,5
		7,2 ±0,4	20,0 ±0,3	
7	09 23 000 9956.00	1,6 ±0,4	13,2 ±0,3	6,7
		4,8 ±0,4	17,0 ±0,3	
8	09 23 000 9957.00	2,4 ±0,4	13,2 ±0,3	5,9
		5,6 ±0,4	17,0 ±0,3	
9	09 23 000 9958.00	3,2 ±0,4	13,2 ±0,3	5,1
		6,4 ±0,4	17,0 ±0,3	
10	09 23 000 9959.00	4,0 ±0,4	13,2 ±0,3	4,3



All Dimensions in mm
Original Size DIN A 3

Techn. Character.

Nicht tolerierte Maßel *free size tolerances*

Dat.

Maßstab/Scale

	Detail
--	--------

03.11

1

Loss

03.11

1 x 1

	Stand.
--	--------

[illegible]

--	--

[illegible]

HAR

6 Elect

0-32

9 ESPECI

--	--

*DIN signal type 2C/2R
shroud press-in*

TB 09 23 000 995x

Blatt / page

