







SECTION X-X
SCALE 20:1



SECTION Y-Y
SCALE 20:1

- 1 PLATED WITH .000030 GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN ON CRIMP BARRELS, ALL OVER .000050 NICKEL UNDERPLATE.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL .000030 TOTAL ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN ON CRIMP BARRELS, ALL OVER .000050 NICKEL UNDERPLATE.
- 2 GOLD FLASH ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000100 TIN PLATED CRIMP BARRELS, ALL OVER .000030 NICKEL UNDERPLATE.
- 3 CRIMP STRIP USING AMP MINI APPLICATOR.
- 4 CONTACT ACCEPTS WIRE RANGE OF 24-28 AWG AND INSULATION RANGE OF .050-.060.

1	1-5066683-0
2	5066683-7
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH SEE TABLE

DWN G. ATTADIA 11-10-04	CHK J. GERACE 11-10-04	APVD M. WALMSLEY 11-10-04
PRODUCT SPEC 108-40005		
APPLICATION SPEC 114-10000		
WEIGHT -		
CUSTOMER DRAWING		

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
SOCKET CONTACT, SIZE 20 DF, AMPLIMITE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-5066683

RESTRICTED TO
-

SCALE
10:1

SHEET
1 OF 1

REV
C