

main menue

- home
- test & measurement
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous

Search

Search

company

- corporate association
- location maps
- fairs and exhibitions
- jobs

home

imprint

contact

terms and conditions

sitemap

Home sockets 4 mm safety system sockets 4 mm safety system SEB 2600 G M4

SEB 2600 G M4

datasheet for SEB 2600 G M4
article number: 972354103



View Full-Size Image



search

Search..

Messetermine

No events

product description:	order number: 972 354-103
description:	Safety built-in socket, 4 mm diameter, touch-protected, M 4 threaded connection and soldering hole, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
typ:	SEB 2600 G M4 gelb/yellow
system:	4 mm safety system
order number:	972 354-103
color versions:	
technical data	
measurement category	CAT II
norm	IEC 61010
type of contact:	spring unloaded socket
type of termination:	screw / solder
rated voltage:	AC/DC 1000 V
rated current:	32 A
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold-plated
housing material:	PA
environmental conditions:	
temperature range:	-40°C to +80°C
inflammable class:	
housing:	94 V-2
drawing	