




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G1	REVISED PER ECO-10-000443	09JUL07	KK	AEG



RECOMMENDED HOLE LAYOUT

- | | |
|---|---|
| 1 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 2 | ASSEMBLIES MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 3 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 4 | .000030 GOLD ON THE CONTACT AREA, .000100—.000200 MATTE TIN—LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL |
| 5 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

		3.984	3.900	39	80	4 - 103783 - 0
5 OBSOLETE		3.884	3.800	38	78	3 - - - 9
		3.784	3.700	37	76	3 - - - 8
		3.684	3.600	36	74	3 - - - 7
		3.584	3.500	35	72	3 - - - 6
		3.484	3.400	34	70	3 - - - 5
		3.284	3.300	33	68	3 - - - 4
		3.284	3.200	32	66	3 - - - 3
		3.184	3.100	31	64	3 - - - 2
		3.084	3.000	30	62	3 - - - 1
5 OBSOLETE		2.984	2.900	29	60	3 - - - 0
		2.884	2.800	28	58	2 - - - 9
		2.784	2.700	27	56	2 - - - 8
		2.684	2.600	26	54	2 - - - 7
		2.584	2.500	25	52	2 - - - 6
		2.484	2.400	24	50	2 - - - 5
		2.384	2.300	23	48	2 - - - 4
		2.284	2.200	22	46	2 - - - 3
		2.184	2.100	21	44	2 - - - 2
5 SUPERCEDED BY 7-146261-0		2.084	2.000	20	42	2 - - - 1
		1.984	1.900	19	40	2 - - - 0
5 OBSOLETE		1.884	1.800	18	38	1 - - - 9
		1.784	1.700	17	36	1 - - - 8
5 OBSOLETE		1.684	1.600	16	34	1 - - - 7
		1.584	1.500	15	32	1 - - - 6
5 SUPERCEDED BY 6-146261-5		1.484	1.400	14	30	1 - - - 5
	5 OBSOLETE		1.384	1.300	13	28
		1.284	1.200	12	26	1 - - - 3
		1.184	1.100	11	24	1 - - - 2
5 OBSOLETE		1.084	1.000	10	22	1 - - - 1
5 OBSOLETE		.984	.900	9	20	1 - - - 0
		.884	.800	8	18	- - - - 9
		.784	.700	7	16	- - - - 8
		.684	.600	6	14	- - - - 7
		.584	.500	5	12	- - - - 6
		.484	.400	4	10	- - - - 5
		.384	.300	3	8	- - - - 4
		.284	.200	2	6	- - - - 3
		.184	.100	1	4	- - - - 2
		.084	-	-	2	103783 - 1
		C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.D.RINGLEY 7-25-85		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK R.ELICKER 7-25-85			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		NAME R.ELICKER PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL HOUSING:FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POSTS		FINISH 		ASSEMBLY, MOD II, HEADER, BREAKAWAY, DOUBLE ROW, .100X .100 CL, WITH .025 SQUARE POSTS SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-103783 -	
		WEIGHT -		CUSTOMER DRAWING SCALE 4:1 SHEET 1 of 1 REV G1	