

5

4

3

2

1

DRAWING NO. CPMC8811-CUST				
REVISIONS				
01 OFFICAL RELEASE				
03-05-09	Z	B	T	Thomas Chow

Description: Stright BNC Crimp Plug For RG58 Style Cable

Part No: CPMC8811

Application: For Cable RG58 Style

Crimp Tool: 24-9958P


Impedance: 50 Ohms

Fequency Range: 0-4 GHz

Material: Body Zinc Nickel Plated
Contact Brass Gold Plated
Insulator PTFE
Crimp Sleeve Brass Nickel Plated
Coupling Nut Zinc Nickel Plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000



DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY GARY.ZHG	DATE 03-05-09
DECIMALS	mm	CHECKED BY TERRY.W	DATE 03-05-09
X	± 0.5	APPROVED BY THOMAS	DATE 03-10-09
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	± 0.5°		

 Connectivity Solutions	
TITLE STRAIGHT BNC CRIMP PLUG FOR R58 STYLE CABLE	
SHEET 1 OF 1	DRAWING NO. CPMC8811-CUST
SIZE A	

受控 CONTROLLED DOCUMENT					
编号 P/N	CPMC8811-CUST	版本 Rev	01	日期 Rel'd Date	Apr29,09

D

D

C

C

B

B

A

A

5

4

3

2

1

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.