



WATERPROOF CAP

SX81



TYPICAL APPLICATIONS

Refrigerators, elettromedical appliances
coffee machines, gardening equipments

FUNCTIONS

- SPST, momentary or not
- SPST illuminated
- SPDT
- SPCO

CYCLE No.

50.000

CUT OUT

30x11 mm

AMBIENT TEMPERATURE

125 °C

GWT


850 °C

GWT NO FLAME (<2sec)

750 °C on demand

S X 8 1 ?


DRAWING




?

TERMINAL


1




2



3





	Z	Y	X
PLASTIC	0,7 ... 3,5	11,0 ±0,1	30,0 +0,2 0
METAL	0,7 ... 2,5	11,0 ±0,1	30,2 +0,2 0

DRAWING	TERMINAL	FUNCTION	RATING	BODY COLOUR	ROCKER COLOUR	MARKING COLOUR	MARKING	LENS COLOUR			
S	X	8	1						0	0	0

?	?	?	?	?	?	?	0	0	0
FUNCTION	RATING	BODY COLOUR	ROCKER COLOUR	MARKING COLOUR	MARKING	LENS COLOUR			
1 1 2	8 Function 1 20 (2) A / 250 VAC * 16 (8) A / 250 VAC 10 (4) A / 400 VAC 10 (6) A / 250 VAC - 5E4 T125/55 °C EN 61058 20 A / 125 VAC 16 A / 250 VAC 3/4 HP - 125 / 250 VAC T105 °C UL 1054 Function 3 - 4 - B 16 (6) A / 250 VAC 10 (4) A / 400 VAC 10 (4) A / 250 VAC - 5E4 T125/55 °C EN 61058 20 A / 125 VAC 16 A / 250 VAC 3/4 HP - 125 / 250 VAC T105 °C UL 1054 Function 5 16 (6) A / 250 VAC 10 (4) A / 250 VAC - 5E4 T125/55 °C EN 61058 16 A - 125 / 250 VAC 3/4 HP - 125 / 250 VAC T105 °C UL 1054 Function 6 20 (2) A / 250 VAC * 16 (8) A / 250 VAC 10 (6) A / 250 VAC - 5E4 T125/55 °C EN 61058 20 A / 125 VAC 16 A / 250 VAC 3/4 HP - 125 / 250 VAC T105 °C UL 1054	1 black 2 white X ? custom	1 black 2 white 9 red ILLUMINATED ✨ G red H orange E green X ? custom	0 none 1 black 2 white X ? custom	0 none 1 none 2 none 6 none A none C none N none X ? custom	0 none ILLUMINATED ✨ G red H orange E green X ? custom			

* Not available with terminal 2