




1 & 3 AMP STANDARD





6 & 10 AMP STANDARD



1 & 3 AMP MEDICAL



6 & 10 AMP MEDICAL



SF 4120	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH	Bleed Resistor MΩ	Connections	Approvals UL	CE	CS
Standard Version								
SF 4120-1/01	1	0.2mA	3.5	Not fitted	6.3 x 0.8 Faston	■	■	■
SF 4120-3/01	3	0.2mA	2.0	Not fitted	6.3 x 0.8 Faston	■	■	■
SF 4120-6/01	6	0.2mA	0.8	Not fitted	6.3 x 0.8 Faston	■	■	■
SF 4120-10/01	10	0.2mA	0.2	Not fitted	6.3 x 0.8 Faston	■	■	■
Medical Version								
SF 4120M-1/01	1	5μA	3.5	1	6.3 x 0.8 Faston	■	■	■
SF 4120M-3/01	3	5μA	2.0	1	6.3 x 0.8 Faston	■	■	■
SF 4120M-6/01	6	5μA	0.8	1	6.3 x 0.8 Faston	■	■	■
SF 4120M-10/01	10	5μA	0.2	1	6.3 x 0.8 Faston	■	■	■


Temperature Range: -25°C to +85°C
Operating Voltage: 250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L+N to ground, 2250Vdc,
 2 seconds

■ Approved
 □ Submitted for Approval

IEC 950 (EN 60950) Applications

DIMENSIONS

All dimensions are nominal and in mm



CIRCUIT DIAGRAMS

