

Standard Barrel Copper Lug

T&B Catalog Number:

54106UF

UPC Number: 78621086864

Status: Active

Description:

Copper One-Hole Lug - 45 degree Standard Barrel - max 35KV, #4 AWG Wire, 1/4" Bolt Size, Tin Plated with Inspection Hole, Grey 29

General

Material	Copper
Finish	Tin Plated
Wire Size	#4 AWG
Number of Studs	1
Stud Size	1/4
Tongue Angle	45
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Grey
Die Code	29

Dimension Information

A (inches)	1.281
B (inches)	.563
C (inches)	.563
D (inches)	.109
E (inches)	.359
F (inches)	.25

Specifications

Voltage Rating 600V to 35KV

Tooling

Connector & Tooling Chart Available on Website

Packaging

Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	1.8 lbs. per 100

Application Support

Overview Available on Website

Notes

Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com