





SPECIFICATIONS

FREQUENCY RANGE: 10 TO 1,000 MHz
 NUMBER OF OUTPUT PORTS: 2
 MINIMUM ISOLATION: 20 dB
 MAXIMUM VSWR: 1.50
 MAXIMUM INSERTION LOSS: 1.50 dB



PASTERNACK ENTERPRISES, INC.

P.O. BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE2003

DES.

BNC FEMALE POWER DIVIDER FREQUENCY RANGE: 10-1000 MHz 2 OUTPUT PORTS

SIZE A

FSCM NO. 53919

CAD FILE 031902

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.