


PCE-7127

LGA1155 Intel® Xeon®/Core™i3/Pentium® SHB
DDR3/SATA 3.0/USB3.0/Dual GbE

NEW



Features

- LGA1155 Intel® Xeon®/Core™i3/Pentium® processors
- Dual Channel (ECC) DDR3 1333/1600 up to 16 GB
- Supports USB3.0, SATA3.0, SW Raid 0, 1, 5, 10, and TPM 1.2 (optional)
- Out-of-band remote management with iAMT8.0 and IPMI (Optional)
- Supports embedded software APIs and utilities

Software APIs:




Utilities:



Specifications

	CPU	Xeon E3-1275V2/ E3-1225V2	Xeon E3-1275/1225	i7-3770	i7-2600	i5-3550S	i5-2400	Core i3-3220	Core i3-2120	Pentium G2120	Pentium G850	Celeron G540
Processor System	Base Frequency	3.5/ 3.2 GHz	3.4/ 3.1 GHz	3.4 GHz	3.4 GHz	3.0 GHz	3.1 GHz	3.3 GHz	3.3 GHz	3.1 GHz	2.9 GHz	2.5 GHz
	L3 Cache	8/ 8 MB	8/ 6 MB	8 MB	8 MB	6 MB	6 MB	3 MB	3 MB	3 MB	3 MB	2MB
	SKU/Chipset	Intel C216										
	BIOS	AMI 64Mbit SPI Flash										
Bus	PCI-Express	One x16 or two x8, plus four x1 to backplane Gen. 2.0										
	PCI	Four 32-bit 33 MHz PCI Masters to backplane										
Memory	Technology	Dual channel(ECC) DDR3 1333/1600										
	Max. Cap.	*Note: ECC supported on Intel Xeon/i3/Pentium processors when paired with Intel C216 PCH 16 GB (8 GB per DIMM)										
	Socket	DDR3 240-pin DIMM x 2										
Graphics	Controller	Chipset integrated Intel HD Graphics										
	VRAM	Shared system memory is subject to OS										
	Video Output	15 Pin VGA D-sub Connector x1/DVI-D connector x 1 (Pin Header)										
Ethernet	Interface	10/100/1000 Mbps										
	Controller	LAN 1: Intel 82579LM LAN 2: Intel 82574L										
	Connector with LED	RJ-45 x 2										
SATA	Ports/Max. Transfer Rate	SATA 2.0 x 4 (300 MB/sec) SATA 3.0 x 2 (600 MB/sec)										
	Raid	SW Raid 0, 1, 5, 10										
I/O Interface	USB	Nine USB2.0 (Pin-header*4+USB Type A*1+ 4 on backplane); Three USB3.0 (Pin-Header*2+Rear*1)										
	Serial	2 x RS-232 Pin-Header										
	Parallel	1 (SPP/EPP/ECP)										
	PS/2	1 (Y cable for mouse and keyboard is included in the package)										
Watchdog Timer	Output	System reset										
	Interval	Programmable 1-255 sec										
Miscellaneous	Audio	Intel High Definition audio interface (Required an audio extension module P/N: PCA-AUDIO-HDA1E)										
Environment	Ambient Temperature	Operating 0 ~ 60° C (32~140° F); Non-operating -40 ~ 85°C and 60° C @ 95% RH Non-Condensing										
	Operating humidity	40° C @ 85% RH Non-Condensing										
Physical	Dimensions	338 mm (L) x 122 mm (W) (13.3" x 4.8")										

Block Diagram



Ordering Information

Part Number	PCH	Memory	Backplane	LAN	VGA	DVI	COM	SATA II	SATA III	USB 2.0	USB 3.0	S/W Raid	iAMT	IPMI
PCE-7127G2-00A1E	C216	ECC/Non-ECC	PCE-5BXX/7BXX*	2	Yes	Yes*	2	4	2	9	3	Yes	Yes	Optional

* Note: 1. PCE-7127 supports all Advantech PCE-5BXX/7BXX backplanes except PCE-7B10-04A1E
2. Output DVI-D signal only (Required DVI-D cable: 1700008822)

Optional Accessories

Part Number	Description
1960047831N001	PCE-7127 Proprietary CPU Cooler (2U)
PCA-AUDIO-HDA1E	Audio extension module
PCA-TPM-00A1E	Trusted Platform Module compliant TCG 1.2
1700020277-01	2 ports of USB 3.0 cable W/ BKT(30cm)
1700008822	DVI-D Cable

Packing List

Part Number	Description	Quantity
1700003194	Serial ATA HDD data cable	x2
1703150102	Serial ATA HDD power cable	x2
1701260305	COM + printer ports cable kit	x1
1700060202	Keyboard and mouse Y-cable	x1
1700008461	4-port USB cable kit	x1
9689000068	Jumper package	x1
2190000902	Warranty Card	x1
2006512700	Startup manual	x1
2066512700	Utility CD	x1

Bracket View



PCE-7127G2-00A1E