

FLOOR ENCLOSURE 400 SERIES 19" x 24" Size Group



Width 22.5" - Depth 24"

Features:

- ▶ Vented on all panels for excellent air circulation characteristics.
- ▶ Top panel features cutouts for fans and cutouts for cable access. Platform features cutouts for cable access.
- ▶ Features 4 fully adjustable internal equipment cage nut rails for #12-24 mounting screws in EIA universal spacing.
- ▶ Comes packaged complete with front door, rear and side panels, leveling feet, casters, grounding bus bar, 2 pre-installed 80 CFM fans and equipment screws.
- ▶ Acrylic framed reversible door.
- ▶ Each enclosure supplied with cage nut hardware set.
- ▶ Meets or exceeds EIA 310D standards.
- ▶ Electrostatic microfinish paint.
- ▶ Ships fully assembled.



Specifications					AWG					
Stock No.	Height	Format	RU	Color	Structure	Side Panels	Top Panel	Rear Panel	Front Door	Base
FE4019-20-01	3'	19"	20 RU	Ivory	18	18	16	18	18	14
FE4019-20-02	3'	19"	20 RU	Black	18	18	16	18	18	14
FE4019-28-01	4'	19"	28 RU	Ivory	18	18	16	18	18	14
FE4019-28-02	4'	19"	28 RU	Black	18	18	16	18	18	14
FE4019-34-01	5'	19"	34 RU	Ivory	16	16	16	16	16	14
FE4019-34-02	5'	19"	34 RU	Black	16	16	16	16	16	14
FE4019-40-01	6'	19"	40 RU	Ivory	16	16	16	16	16	14
FE4019-40-02	6'	19"	40 RU	Black	16	16	16	16	16	14
FE4019-45-01	7'	19"	45 RU	Ivory	16	16	16	16	16	14
FE4019-45-02	7'	19"	45 RU	Black	16	16	16	16	16	14

RU = Rack Units

Quest Manufacturing



FLOOR ENCLOSURE 400 SERIES 19" x 24" Size Group

Width 22.5" - Depth 24"

Cable Access




Top panel features cutouts for cable access.

Removable Panels




Removable side and rear panels utilizing dual latching keepers and keyed for security.

Adjustable Rails



Features 4 fully adjustable internal equipment cage nut rails for #12-24 mounting screws in EIA universal spacing.

Vented Panels



Vented panels for excellent air circulation characteristics.



Smoked Acrylic

FLOOR ENCLOSURE 400 SERIES

19" x 24" Size Group



Width 22.5" - Depth 24"



External Dimensions

Product					Package			
RU	A - Height	B - Width	C - Depth	Load Capacity	Height	Width	Depth	Shipping Weight
20 RU	3'	22.5"	24"	630 lbs	42.5"	25"	26.5"	117 lbs
28 RU	4'	22.5"	24"	650 lbs	57.5"	25"	26.5"	133 lbs
34 RU	5'	22.5"	24"	700 lbs	67.5"	25"	26.5"	175 lbs
40 RU	6'	22.5"	24"	730 lbs	78.5"	25"	26.5"	238 lbs
45 RU	7'	22.5"	24"	830 lbs	88.5"	25"	26.5"	258 lbs

RU = Rack Units

Internal Dimensions

Product				
RU	A - Height	B - Width	C - Depth	Load Capacity
20 RU	35"	20.1"	21.5"	630 lbs
28 RU	47"	20.1"	21.5"	650 lbs
34 RU	59.5"	20.1"	21.5"	700 lbs
40 RU	70"	20.1"	21.5"	730 lbs
45 RU	78.75"	20.1"	21.5"	830 lbs



Colors:



Black



Ivory

Custom colors and configurations available. Minimum quantities apply.