

Multi-Purpose Mini Shotgun Microphone



A multi-pupose miniature shotgun style microphone suitable for overhead, desktop or mobile use. Supplied with hanging cable, cast desktop base and a screw-fix mount the microphone can be used for most applications.

- Flexible, multi-purpose shotgun microphone
- High SPL handling
- Excellent feedback rejection
- Overhead, movable besktop and unmovable desktop options
- Supplied with two bases, 10m hanging cable, Mini-XLr to XLR adaptor, microphone holder and hanging spring
- Dimensions:
Shotgun mic: $\varnothing$ 15x140mm
Movable base (mic. holder included): $\varnothing$ 100x98mm (H)
Unmivable base (mic. holder included): $\varnothing$ 45x72mm (H)

Frequency Range	30Hz to 18kHz	Maximum SPL	119dB @ 1kHz
Element	Back Electret-Condenser	Dynamic Range	89dB @ 1kHz
Polar Pattern	Line + Gradient	Signal-to-noise Ratio	64db, 1kHz at 1Pa
Impedance	200 Ω	Power	9-52V DC Phantom Power
383360.345390			

Order Code		Price Each
867-0463		