





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005027	11MAR11	RK	HMR
	C	REVISED PER ECO-16-006378	03NOV2016	RS	MZ

D

C

B

A



788158-3 ONLY

- THIS PART WILL ACCEPT NINE (9) MULTIMATE PIN CONTACTS.
- HOUSING AND PRESSURE PLATE: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, GRAY.
WIRE ENTRY SEAL: ELASTOMER, RED-IRON OXIDE.
THREADED INSERTS: BRASS.
- OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

3	OBsolete	YES	.040-.080	SMALL	788158-3
		NO	.065-.100	STANDARD	788158-2
3	OBsolete	NO	.040-.080	SMALL	788158-1
		THREADED INSERTS	WIRE INSULATION DIAMETER RANGE	INSULATION	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.DORWART 26 AUG 98	TE Connectivity	
DIMENSIONS: mm [INCHES]			CHK R.WALTER 26 AUG 98		
			APVD R.WALTER 26 AUG 98	NAME	
			PRODUCT SPEC		
			APPLICATION SPEC	RECEPTACLE ASSEMBLY, 13-9, STANDARD SEX, SERIES I, SEALED, CIRCULAR PLASTIC CONNECTOR	
			WEIGHT		
MATERIAL 2			CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779
				DRAWING NO C=788158	RESTRICTED TO
				SCALE 2:1	SHEET 1 OF 1
					REV C