

Wall-mounting steel enclosures

Selection guide



Specifications						Spacial S3D								
						Plain door			Glazed door	Plain mounting plate	Silkscreened mounting plate (2)			
Dimensions (1)			N° of doors	IP	Weight (kg)*	With mounting plate	Without mounting plate	Without mounting plate						
						Page 2/8			Page 7/2					
H	W	D	300	200	150	1	66	3.02	NSYS3D3215P	NSYS3D3215		NSYS3D3215T	NSYMM32	
			300	250	150	1	66	3.48	NSYS3D32515P	NSYS3D32515		NSYS3D32515T	NSYMM3025	
			300	300	150	1	66	3.90	NSYS3D3315P	NSYS3D3315		NSYS3D3315T	NSYMM33	
			300	300	200	1	66	4.50	NSYS3D3320P	NSYS3D3320		NSYS3D3320T	NSYMM33	
			300	400	150	1	66	4.82	NSYS3D3415P	NSYS3D3415		NSYS3D3415T	NSYMM43	NSYMS43
			300	400	200	1	66	5.60	NSYS3D3420P	NSYS3D3420		NSYS3D3420T	NSYMM43	NSYMS43
			400	300	150	1	66	4.90	NSYS3D4315P	NSYS3D4315		NSYS3D4315T	NSYMM43	NSYMS43
			400	300	200	1	66	5.00	NSYS3D4320P	NSYS3D4320		NSYS3D4320T	NSYMM43	NSYMS43
			400	400	200	1	66	6.50	NSYS3D4420P	NSYS3D4420		NSYS3D4420T	NSYMM44	NSYMS44
			400	600	200	1	66	10.50	NSYS3D4620P	NSYS3D4620		NSYS3D4620T	NSYMM64	NSYMS64
			400	600	250	1	66	12.00	NSYS3D4625P	NSYS3D4625		NSYS3D4625T	NSYMM64	NSYMS64
			500	300	200	1	66	7.50	NSYS3D5320P	NSYS3D5320		NSYS3D5320T	NSYMM53	NSYMS53
			500	400	200	1	66	9.30	NSYS3D5420P	NSYS3D5420		NSYS3D5420T	NSYMM54	NSYMS54
			500	400	250	1	66	10.20	NSYS3D5425P	NSYS3D5425		NSYS3D5425T	NSYMM54	NSYMS54
			500	500	200	1	66	11.18	NSYS3D5520P	NSYS3D5520		NSYS3D5520T	NSYMM55	NSYMS55
			500	500	250	1	66	12.06	NSYS3D5525P	NSYS3D5525		NSYS3D5525T	NSYMM55	NSYMS55
			600	400	200	1	66	11.00	NSYS3D6420P	NSYS3D6420		NSYS3D6420T	NSYMM64	NSYMS64
			600	400	250	1	66	12.00	NSYS3D6425P	NSYS3D6425		NSYS3D6425T	NSYMM64	NSYMS64
			600	500	250	1	66	16.20	NSYS3D6525P	NSYS3D6525		NSYS3D6525T	NSYMM65	
			600	600	200	1	66	14.00	NSYS3D6620P	NSYS3D6620		NSYS3D6620T	NSYMM66	NSYMS66
			600	600	250	1	66	15.00	NSYS3D6625P	NSYS3D6625		NSYS3D6625T	NSYMM66	NSYMS66
			600	600	300	1	66	17.00	NSYS3D6630P	NSYS3D6630		NSYS3D6630T	NSYMM66	NSYMS66
			600	600	400	1	66	19.00	NSYS3D6640P	NSYS3D6640		NSYS3D6640T	NSYMM66	NSYMS66
			600	800	300	1	66	25.50	NSYS3D6830P	NSYS3D6830		NSYS3D6830T	NSYMM86	NSYMS86
			700	500	250	1	66	15.00	NSYS3D7525P	NSYS3D7525		NSYS3D7525T	NSYMM75	NSYMS75
			800	600	200	1	66	21.00	NSYS3D8620P	NSYS3D8620		NSYS3D8620T	NSYMM86	NSYMS86
			800	600	250	1	66	23.00	NSYS3D8625P	NSYS3D8625		NSYS3D8625T	NSYMM86	NSYMS86
			800	600	300	1	66	25.00	NSYS3D8630P	NSYS3D8630		NSYS3D8630T	NSYMM86	NSYMS86
			800	600	400	1	66	29.00	NSYS3D8640P	NSYS3D8640		NSYS3D8640T	NSYMM86	NSYMS86
			800	800	250	1	66	30.00	NSYS3D8825P	NSYS3D8825		NSYS3D8825T	NSYMM88	
			800	800	300	1	66	32.00	NSYS3D8830P	NSYS3D8830		NSYS3D8830T	NSYMM88	
			800	1000	300	1	66	38.00	NSYS3D81030P	NSYS3D81030			NSYMM108	
			800	1000	300	2	55	43.50	NSYS3D81030DP	NSYS3D81030D			NSYMM108	
			800	1200	300	2	55	46.00	NSYS3D81230DP	NSYS3D81230D			NSYMM128	
			1000	600	250	1	66	28.00	NSYS3D10625P	NSYS3D10625		NSYS3D10625T	NSYMM106	
			1000	600	300	1	66	30.60	NSYS3D10630P	NSYS3D10630		NSYS3D10630T	NSYMM106	
			1000	600	400	1	66	33.00	NSYS3D10640P	NSYS3D10640		NSYS3D10640T	NSYMM106	
			1000	800	250	1	66	35.00	NSYS3D10825P	NSYS3D10825		NSYS3D10825T	NSYMM108	
			1000	800	300	1	66	38.00	NSYS3D10830P	NSYS3D10830		NSYS3D10830T	NSYMM108	
			1000	800	400	1	66	42.00	NSYS3D10840P	NSYS3D10840		NSYS3D10840T	NSYMM108	
			1000	1000	300	1	66	46.00	NSYS3D101030P	NSYS3D101030		NSYS3D101030T	NSYMM1010	
			1000	1000	300	2	55	46.00	NSYS3D101030DP	NSYS3D101030D		NSYS3D101030DT	NSYMM1010	
			1000	1200	300	2	55	53.00	NSYS3D101230DP	NSYS3D101230D			NSYMM1210	
			1000	1200	400	2	55	60.00	NSYS3D101240DP	NSYS3D101240D			NSYMM1210	
			1200	600	300	1	66	37.00	NSYS3D12630P	NSYS3D12630		NSYS3D12630T	NSYMM126	
			1200	600	400	1	66	42.00	NSYS3D12640P	NSYS3D12640		NSYS3D12640T	NSYMM126	
			1200	800	300	1	66	45.00	NSYS3D12830P	NSYS3D12830		NSYS3D12830T	NSYMM128	
			1200	800	400	1	66	49.00	NSYS3D12840P	NSYS3D12840		NSYS3D12840T	NSYMM128	
			1200	1000	300	1	66	53.00	NSYS3D121030P	NSYS3D121030		NSYS3D121030T	NSYMM1210	
			1200	1000	300	2	55	54.00	NSYS3D121030DP	NSYS3D121030D		NSYS3D121030DT	NSYMM1210	
			1200	1000	400	2	55	61.00	NSYS3D121040DP	NSYS3D121040D			NSYMM1210	
			1200	1200	300	2	55	64.00	NSYS3D121230DP	NSYS3D121230D			NSYMM1212	
			1200	1200	400	2	55	90.00	NSYS3D121240DP	NSYS3D121240D			NSYMM1212	
			1400	1000	300	2	55	80.00	NSYS3D141030DP	NSYS3D141030D			NSYMM1410	

(1) For other dimensions, see our application offer.
 (2) In inverted use, the marking is inverted.

*Enclosure without mounting plate.

