





REV. 更改	DESCRIPTION 說明	ENG. 修改人	APPROVE 審核



CONTACT CONFIGURATION



"x"	LED Color
R	Red
G	Green
Y	Yellow
O	Orange
B	Blue
W	White



SPECIFICATIONS:

- 1.Contact Rating: 2A @ 36VDC.
- 2.Electrical Life: 50,000cycles.
- 3.Contact Resistance: 50m-ohms max (initial).
- 4.Insulation Resistance: 1,000M-ohms min @ 500VDC.
- 5.Dielectric Strength: 2,000V RMS 50~60Hz.
- 6.Operating Temperature: -20°C ~ +55°C.
- 7.Switching Circuit: OFF-MOM.
- 8.Torque: 5~14Nm max. applied to nut.
- 9.Operating Force: 4N max.
- 10.IP Class: IP65 protection.

MATERIALS:

- 1.Bushing & Button: Refer to table
- 2.Contact: Silver alloy.
- 3.Nut: Nickel plated brass.
- 4.Base: PBT.

Code	Bushing Material	MOQ
B3	Nickel plated brass with varnished polished	2000PCS
B32	Stainless steel with varnished polished	100PCS

ITEM NO. 料 號	AV01L-B32-M3-FR-B-6V
-----------------	----------------------

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF TAIWAY ELECTRONICS LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF TAIWAY ELECTRONICS LTD.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: ±1.0°

DIMENSIONS	TOLERANCE
0.00 TO 30.00mm	±0.20mm
30.01 TO 80.00mm	±0.25mm
80.01 TO 150.00mm	±0.30mm
150.01 +	±0.40mm

MATERIAL

泰瑋電子有限公司
TAIWAY ELECTRONICS COMPONENTS CO.,LTD.

USED 用途 AV	APPD. 審核 Amy 2008/10/14
FINISH 處理	CHKD. 校對 Amy 2008/10/14
SCALE 比例 2 / 1	DR. 製圖 Amy 2008/10/14
TITLE 名稱 Anti-Vandal Switch	
DWG NO. 圖號 AV01L-B32-M3-FR-B-6V	
FILE NAME 檔案名稱 AV01LB3M3FR.DWG	SHEET 張 1 / 1
REV. 更改	1

SIZE
圖紙 A4