

Housing - HC-STA-B24-SLWD-2SSP21-ELC-AL - 1412875

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting bases B24, With double locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 2, lateral, Height: 68 mm, Cable gland: none, Gland: Yes, 2x Pg21, Standard

Why buy this product

- good shielding in the event of electromagnetic interference



Key Commercial Data

Packing unit	1 STK
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	68 mm
Width	57 mm
Length	144 mm

Ambient conditions

Degree of protection of housing (IP)	IP66 (for HC-EVO... / HC-STA... metal sleeve housing)
	IP69K (ISO 20653:2013-02, with suitable cable gland/suitable filler plug, for HC-EVO... / HC-STA... metal sleeve housing)
	IP67 (with suitable screw connection/suitable filler plug, for HC-STA... metal sleeve housing)
Degree of protection of housing (NEMA)	4
	4X
	12

Housing - HC-STA-B24-SLWD-2SSP21-ELC-AL - 1412875

Technical data

Ambient conditions


Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

General

Note	for contact inserts HC-B24, BB46, D64, DD108, HV10/16, M
Size	B24
Housing type	Box mounting bases
Locking type	With double locking latch
No. of cable outlets	2
Cable exit	lateral
Screw connection	none
Type of the screw connection	2x Pg21
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	Uncoated
Material lock	PA
Assembly instructions	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27143423
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

Housing - HC-STA-B24-SLWD-2SSP21-ELC-AL - 1412875

Classifications

ETIM

ETIM 5.0	EC000437
----------	----------

Approvals

Approvals

Approvals

EAC / GL

Ex Approvals

Approvals submitted

Approval details

EAC

GL

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG21-M68N-NNES-S - 1411175



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 13 mm ... 18 mm, Shielding: No, Connecting thread: Pg21, Color: silver

Housing - HC-STA-B24-SLWD-2SSP21-ELC-AL - 1412875

Accessories

Cable gland - G-INSEC-PG21-M68N-NNES-S - 1411200



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 13 mm ... 18 mm, Shielding: yes, Connecting thread: Pg21, Color: silver

Housing latches

Housing brackets - HC-STA-B10-24-DL-PLBK - 1412886



Double locking latch for B10 / B16 / B24 housing, HC-EVO....AL and HC-STA....AL

Seal

Profile gasket - HC-B24-SP-CBK - 1411482



Profile gasket for HEAVYCON EVO supporting base element type B24, conductive