

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300060356

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 18 AWG, PVC Cable, 15.0m (49.21') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

130006

Mini-Change

Pigtail

IP67

Copper Alloy

Brad Mini-Change Connectors

Mini-Change

N/A

America

Single Ended

78678840828

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Net Weight

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

7.14mm (.281")

15.0m (49.21')

Yellow

Threaded

Female-Pigtail

Single

No

PVC

PVC

Black Epoxy Coated Zinc

Gold

1211.000/g

Straight to Pigtail

3

-20°C to +105°C

18

AWM 2661

Electrical

Current - Maximum per Contact

Voltage - Maximum

10.0A

300V

Material Info


Engineering Number

103000A06M150

Reference - Drawing Numbers

Sales Drawing

SD-130006-009



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130006 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION