


KZL

Strain relief plates



Product description

The strain relief plate KZL range is used for static or dynamic applications for organizing and securing cables on machines, control panels or drag chains.

The undercut on the comb-shaped profile provides secure strain relief according to EN 50262. Strain relief of the cables is achieved by using cable ties.

Strain relief plates are available for 30 mm DIN rails shape C or 35 mm DIN rails shape H.

Advantages

- Simple assembly
- Cost-effective
- High packing density
- Universal usage

Specification

Material **Polyamide (PA)**
 Flame class **UL94-Vo, self-extinguishing**
 Temperature **40°C to +140°C (static)**
 Properties **Halogen-free, silicone-free**

Accessories

KB Cable ties **Page 73**
 DIN rails **Page 91**

Type	Order No. for H-rails	Order No. for C-rails	Length L1	Length L2	No. of teeth	PU
KZL 39	32260	32261	38.5 mm	28.3 mm	3	10
KZL 80	32262	32263	79.5 mm	68.0 mm	6	10
KZL 140	32264	32265	139.5 mm	128.1 mm	9	10