



| PLATING SPECIFICATIONS |                 |                         |
|------------------------|-----------------|-------------------------|
|                        | CONTACT         | TERMINAL                |
| A                      | .000015" GOLD   | .0001" TIN/LEAD         |
| D                      | .00003" GOLD    | .00003" GOLD OVERALL    |
| G                      | .00001" GOLD    | .000005" GOLD           |
| M                      | .00003" GOLD    | .00001" GOLD OVERALL    |
| N                      | .00005" GOLD    | .0001" TIN/LEAD         |
| O                      | .00003" GOLD    | .0001" TIN/LEAD         |
| P                      | GOLD FLASH      | GOLD FLASH              |
| R                      | .00002" GOLD    | .0001" TIN/LEAD         |
| S                      | .00001" GOLD    | .00001" GOLD OVERALL    |
| T                      | .0001" TIN/LEAD | .0001" TIN/LEAD OVERALL |
| V                      | .00003" GOLD    | .000005" GOLD           |
| W                      | GOLD FLASH      | .0001" TIN/LEAD         |
| X                      | .00003" GOLD    | .0001" TIN/LEAD         |
| Y                      | .00003" GOLD    | .000005" GOLD           |
| Z                      | .00001" GOLD    | .0001" TIN/LEAD         |

| PART NUMBER  | CONTACT PIN | HEAD LENGTH  | TAIL LENGTH  |
|--------------|-------------|--------------|--------------|
| GTC_SABN-M30 | ETC-SAB     | 0.230 [5.84] | 0.320 [8.13] |
| GZC_SABN-M30 | EZC-SAB     | 0.230 [5.84] | 0.320 [8.13] |
| GTC_SFBN-M30 | ETC-SFB     | 0.318 [8.08] | 0.300 [7.62] |
| GZC_SFBN-M30 | EZC-SFB     | 0.318 [8.08] | 0.300 [7.62] |



| PART NUMBER  | BODY NUMBER | A             |
|--------------|-------------|---------------|
| G_C01S_N-M30 | H01S-A360   | 0.100 [2.54]  |
| G_C02S_N-M30 | H02S-A360   | 0.200 [5.08]  |
| G_C03S_N-M30 | H03S-A360   | 0.300 [7.62]  |
| G_C04S_N-M30 | H04S-A360   | 0.400 [10.16] |
| G_C05S_N-M30 | H05S-A360   | 0.500 [12.70] |
| G_C06S_N-M30 | H06S-A360   | 0.600 [15.24] |
| G_C07S_N-M30 | H07S-A360   | 0.700 [17.78] |
| G_C08S_N-M30 | H08S-A360   | 0.800 [20.32] |
| G_C09S_N-M30 | H09S-A360   | 0.900 [22.86] |
| G_C10S_N-M30 | H10S-A360   | 1.000 [25.40] |
| G_C11S_N-M30 | H11S-A360   | 1.100 [27.94] |
| G_C12S_N-M30 | H12S-A360   | 1.200 [30.48] |
| G_C13S_N-M30 | H13S-A360   | 1.300 [33.02] |
| G_C14S_N-M30 | H14S-A360   | 1.400 [35.56] |
| G_C15S_N-M30 | H15S-A360   | 1.500 [38.10] |
| G_C16S_N-M30 | H16S-A360   | 1.600 [40.64] |
| G_C17S_N-M30 | H17S-A360   | 1.700 [43.18] |
| G_C18S_N-M30 | H18S-A360   | 1.800 [45.72] |
| G_C19S_N-M30 | H19S-A360   | 1.900 [48.26] |
| G_C20S_N-M30 | H20S-A360   | 2.000 [50.80] |
| G_C21S_N-M30 | H21S-A360   | 2.100 [53.34] |
| G_C22S_N-M30 | H22S-A360   | 2.200 [55.88] |
| G_C23S_N-M30 | H23S-A360   | 2.300 [58.42] |
| G_C24S_N-M30 | H24S-A360   | 2.400 [60.96] |
| G_C25S_N-M30 | H25S-A360   | 2.500 [63.50] |
| G_C26S_N-M30 | H26S-A360   | 2.600 [66.04] |
| G_C27S_N-M30 | H27S-A360   | 2.700 [68.58] |
| G_C28S_N-M30 | H28S-A360   | 2.800 [71.12] |
| G_C29S_N-M30 | H29S-A360   | 2.900 [73.66] |
| G_C30S_N-M30 | H30S-A360   | 3.000 [76.20] |
| G_C31S_N-M30 | H31S-A360   | 3.100 [78.74] |
| G_C32S_N-M30 | H32S-A360   | 3.200 [81.28] |
| G_C33S_N-M30 | H33S-A360   | 3.300 [83.82] |
| G_C34S_N-M30 | H34S-A360   | 3.400 [86.36] |
| G_C35S_N-M30 | H35S-A360   | 3.500 [88.90] |
| G_C36S_N-M30 | H36S-A360   | 3.600 [91.44] |

COMPUTER  
GENERATED  
DOCUMENT DO  
NOT CHANGE  
MANUALLY

**PROPRIETARY AND CONFIDENTIAL**

THIS DRAWING AND DESIGN IS THE PROPERTY OF SULLINS ELECTRONICS. IT MAY NOT BE USED FOR ANY PURPOSE OTHER THAN BY THE OWNER. SULLINS ELECTRONICS DOES NOT AUTHORIZE THE REPRODUCTION OR CONVEYANCE OF ANY INFORMATION CONTAINED HEREIN.

|           |         |                                                                                                                                                                                                   |  |                                                    |                 |                   |
|-----------|---------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------|-----------------|-------------------|
| A         | 62      | ORIGINAL RELEASE                                                                                                                                                                                  |  | 9/19/03                                            | JFW             | AJT               |
| REV.      | ECO NO. | DESCRIPTION                                                                                                                                                                                       |  | DATE                                               | BY              | APP'VD            |
|           |         | UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES<br>TOLERANCES<br>FRACTIONAL ± 1/32<br>ANGULAR ± 1°<br>TWO PLACE DECIMAL ± .02<br>THREE PLACE DECIMAL ± .005<br>FOUR PLACE DECIMAL ± .0005 |  | DRAWN<br>9/19/03                                   | DATE<br>9/19/03 | NAME<br>JWHITE    |
|           |         | INTERPRET GEOMETRIC TOLERANCING PER:                                                                                                                                                              |  | CHECKED<br>9/19/03                                 | AJT             |                   |
|           |         | MATERIAL NOTED                                                                                                                                                                                    |  | COMMENTS:                                          |                 |                   |
|           |         | FINISH N/A                                                                                                                                                                                        |  | PART NO./DESCRIPTION:<br>HEADERS<br>G_C__S__ N-M30 |                 |                   |
| NEXT ASSY | USED ON | DO NOT SCALE DRAWING                                                                                                                                                                              |  | SIZE<br><b>C</b>                                   |                 | DWG. NO.<br>10058 |
|           |         |                                                                                                                                                                                                   |  | SCALE: 1:1                                         |                 | REV<br>A          |
|           |         |                                                                                                                                                                                                   |  | SHEET 1 OF 1                                       |                 |                   |