


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)												
PLP1S	.06 (1.5)	1.00 (25.4)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	5.3 (135)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.24 (109)
PLP1.5S	.06 (1.5)	1.50 (38.1)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	6.7 (170)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.29 (132)
PLP2S	.06 (1.5)	1.75 (44.5)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	7.88 (200)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.32 (145)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

2) SEE DRAWING SS-26888(A) FOR PLP1.5I.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE						
							STRAP, PUSH MOUNT-PLP						
							CUSTOMER DRAWING						
							ITEM REVISION NAME		SS-26803/AB				
							DATASET FILE NAME		SS-26803_DC/AB SS-26803_REV07				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:	
							.x ± .1 [2.5] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± - - - -					NYLON 6.6	
							 THIRD ANGLE PROJECTION				DRAWING NUMBER:		
07	11/04/14	BWG	MPH	JADE	CHANGED "B" DIMENSION TO .190 AND UPDATED TITLE BORDER AND NOTES. SEE ECN FOR COMPLETE DETAILS.	SS-26803/07						SS - 26803	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE		
							RAM	4/27/93	HVP	NONE	A		
											SHT 1 OF 1		