

6, 8, 10 and 12-Wire Receptacles, Rear Mount with Leads

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 60 VAC/75 VDC, 2 A



Housing Style	Female Part Number	Male Part Number	Features	Pinout
FKFD .. Typical panel cutout is 15.3 x 14 mm.	FKFD 8-*	FSFD 8-*	8x24 AWG, 105°C, mates with 8-pin cordsets, UL Recognized, CSA Approved	Female Male
	FKFD 8-*/S1505	FSFD 8-*/S1505	8x26 AWG, 105°C, mates with 8-pin cordsets	Female Male
	FKFD 10-*	FSFD 10-*	10x24 AWG, 105°C, mates with 10-pin cordsets	Female Male
FSFD ..* Typical panel cutout is 15.3 x 14 mm.	FKFD 12-*	FSFD 12-*	12x24 AWG, 105°C, mates with 12-pin cordsets	Female Male

* Length in meters. Standard lead length is 0.5 meters. Consult factory for other lengths.
Standard housing material is nickel plated brass "FSFD.."; "FSFDV.." indicates stainless steel.
To specify PVC jacketed cable, add "/S717" to the end of the part number.