




LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
BD	20				D	REDRAWN	8/12/91	-
					E	REV PER EC0020-1394-93	12/20/93	SK



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 2.54µm [.000100] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- 3 TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 4 ACCEPTS #2 SELF-TAPPING SCREW, .250 LONG REF.
- 5 MATES WITH 8 POSITION SHIELDED DIN PLUG 212437-6.
- 6 BRASS PER ASTM B36.



212034-1
PART NO.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm[INCHES] TOLERANCES ON : 2 PLC DEC ±0.13(.005) 3 PLC DEC ± - ANGLES ± 0°30'	DR 8/12/91 A.STAUB BG		AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 11/22/91 J. MCCLINTON				
	APPD 11/22/91 D. ROCKER		NAME RECEPTACLE ASSY, RIGHT ANGLE, SHIELDED, 8 POSITION, W/MTG HOLES, CIRCULAR DIN		
	APPD 11/22/91 C. ROHDE				
MATERIAL HOUSING: 1 CONTACTS: 6 RECEPTACLE SHIELD: 6	PRODUCT SPEC 108-10047		SIZE C CAGE CODE 00779 DRAWING NO 212034		
	APPLICATION SPEC 114-40025				
FINISH FINISH: 3 CONTACTS: 2 RECEPTACLE SHIELD: 2	WEIGHT -		SCALE 4:1		SHEET 1 OF 1