



FEATURES:

- True 75 Ohm connectors for optimal impedance match
- Highly flexible multi-stranded 75 Ohm RG59 type coax cable
- Red and Blue colored cables allow distinction between transmit and receive lines.

MATERIALS:

Connectors: BNC Male

Body: Brass, Tarnish resistant plating

Dielectric: PTFE

Center Contact – Gold Plated Brass

Strain Relief: PVC molded directly to cable and connectors

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 6510-V-XX-*

XX = Cable length, standard lengths = Black: 12" (304,8), 24" (609,8), 36" (914,4), 48" (1219,2), 60" (1524,0),
Black, Red & Blue: 72" (1828,8)

*= Standard Color: 0-Black, 2-Red, 6-Blue

Ordering Example: Model 6510-V-48-2, Cable Length is 48" (1219,2) Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA