THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
–	RELEASED FROM ENGINEERING	4/1/04	

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	1.5	W
MAX INPUT POWER	3.0	W
IMPEDANCE	45±15	OHM
OUTPUT SPL @ 1W/0.5M (AT 0.8, 1.0, 1.2, 1.5 kHz)	86±3	dBA
DISTORTION	5%	–
RESONANT FREQUENCY	360±20%	Hz
FREQUENCY RANGE	360 ~ 7,000	Hz
HOUSING MATERIAL	METAL	–
CONE MATERIAL	PAPER	–
MAGNET MATERIAL	FERRITE	–
OPERATING TEMPERATURE	−20 ~ +85	℃
WEIGHT	60	grams



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN R.A.C.	3/04
APPROVED R.W.	3/04

FILE NAME
AS07245PO.DWG

DO NOT SCALE DRAWING

projects ® unlimited Dayton , Ohio

SPEAKER
AS07245PO

SIZE A | DRAWING NO. AS07245PO

SCALE: N.T.S. | SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PUI Audio:
AS07245PO