



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor


[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'HS2X2LG6NM'

Your search criteria matched only one product, shown below

HS2X2LG6NM



Type HS Raceway is ideal for applications that require easy access in control panels and communication closets for frequent equipment modifications or repairs where moves, adds and changes are common. Due to the hinging feature, Hinged Cover Solid Wall Raceway reduces the time and hassle associated with removing and reinstalling traditional raceway cover to perform maintenance or changes.

Specifications

- Material: Lead-free PVC
- Rated for continuous use temperature: 122°F (50°C)
- UL94 flammability rating V -0
- Conforms with NFPA 79 -2007 section 13.3.1 requirement for flame retardant material
- Base and cover length is 6 feet

Features and Benefits

- Integrated hinged cover design allows easy access to wiring without hassle of removing and reinstalling cover

- Dual-sided hinge can open up to 100° from either sidewall of duct base for easy access to channel
- Cover retention flanges allows the cover to open and close easily
- Base scoreline allows sidewall sections to be more easily removed
- Cover removal rib makes cover easy to open from either side

Base and cover sold separately.

Part Number	HS2X2LG6NM
RoHS Compliancy Status	Compliant
Part Description	Solid wall hinged wiring duct.
Material	Lead– Free PVC
Color	Light Gray
Length (ft.)	6
Duct Size W x H (In.)	2.17 x 1.98
Duct Size W x H (mm)	55.1 x 50.3
Pricing Description	Solid Hinged Duct,PVC,2"X2"X6',Light Gray,NM
Cover Part Number	HC2LG6
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.