




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIMENSIONS							WEIGHT grams/ 100 pcs
	'A'	'B'	'C'	'D'	'E'	'F'	'G'	
CSEH15A30-_20	18.6	31	26.8	30	11.6	8	13.2	833
CSEH15A30-_0								
CSEH15A30-_100								



NOTES:

- MATERIAL:
 - _20 NYLON 6/6
 - _0 NYLON 6/6 UV STABILIZED
 - _100 POLYPROPYLENE UV STABILIZED IMPACT MODIFIED
- COLOR: -_20, -_0, & -_100 BLACK
- FOR USE WITH PANDUIT CABLE TIE TYPE:
 - M- MINATURE
 - I- INTERMEDIATE
 - S- STANDARD
 - H- HEAVY
 - EH- EXTRA HEAVY
- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION PACKAGE SIZE AND COLOR.



DIMENSIONS ARE METRIC [mm]	
CND FILENAME/LAYER# G1932BV_PB_CSEH15A30_00	
PANDUIT CORP. TINLEY PARK, ILLINOIS	
SPACER	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ±0.5mm	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN METRIC, THIRD ANGLE PROJECTION.
DRAWN BY JAD DATE 4/28/03 CHK'D	MAT'L: SEE NOTE 1 SCALE NONE DRAWING NO. G1932BV CND SIZE A

R	4/28/03	JAD		INITIAL RELEASE	GB1932BV	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	