



THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	12	Vdc
OPERATING VOLTAGE RANGE	8 ~ 18	Vdc
RATED CURRENT (MAX)	35	mA
MINIMUM SPL @ 10 cm	86	dBA
RESONANT FREQUENCY	60±10	Hz
TONE OR PULSE RATE	CONTINUOUS	0 PULSE PER SECOND
OPERATING TEMPERATURE	-20 ~+ 60	°C
STORAGE TEMPERATURE	-30 ~ +70	°C
HOUSING MATERIAL	NONE	-
TERMINAL MATERIAL	QUICK DISCONNECT TABS	-
WEIGHT	27	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	5/2/02	
A	REVISED SPL, WEIGHT & TO NEW TEMPLATE	8/02/05	B.R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AI-291.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>RABL</i>	05/02
CHECKED <i>S.J.</i>	05/02
APPROVED <i>S.J.</i>	05/07/02

DO NOT SCALE DRAWING



projects®
unlimited

Dayton , Ohio

AUDIO INDICATOR

SIZE
A

DRAWING NO.
AI291.DWG

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-291](#)