



H100X044F1T







- Labels offer crisp, clear legends with superior legibility
- Meets UL Standard 224 for flammability and UL Standard 2043 suitable for use in air handling spaces
- Shrink ratio 3:1
- Pre-cut flattened polyolefin is both thermal transfer and dot matrix printable and supplied roll mounted on plastic carrier
- *PANDUIT* labeling software packages include all label formats for quick and easy label production

■ Part Number	H100X044F1T
■ RoHS Compliancy Status	Compliant
■ Note	H100X044F1T replaces LHS25W2
■ Part Description	White, 1/4" diameter polyolefin, 1000/roll.
■ Material	3:1 Flattened Polyolefin
■ Color	White
■ Diameter (In.)	.25
■ Diameter (mm)	6.35
■ Length (In.)	.44
■ Length (mm)	11.18
■ Width (In.)	1.00
■ Width (mm)	25.40
■ Markers Per Roll	1000
■ Markers Per Row	2
■ Max. Wire O.D. (In.)	.25
■ Max. Wire O.D. (mm)	6.35
■ Min. Cable O.D. (In.)	.08
■ Min. Cable O.D. (mm)	2.03
■ Nominal Cable O.D. (In.)	.08 - .25
■ Nominal Cable O.D. (mm)	2.03 - 6.35
■ Pricing Description	ThermTrans, Heatshrink Tubing, Polyolefin, 1.00" W x .44" H, White, 1000 pieces
■ Web Width (In.)	3.50
■ Min. Order UOM	RL
■ Min. Order Qty.	1
■ BOM Qty. (# of Pkgs.)	



FINISHED PRODUCT
UNWIND DIRECTION
AWAY FROM LID OF BOX



PART NUMBER	SEE DETAIL	"A"	"B"	"C"	MARKER ACROSS	TUBING COLOR
H200X034F1T	A	2.00	3.50	0.335	1	WHITE
H100X034F1T	B	1.00	3.50	0.335	2	WHITE
H050X034F1T	C	0.50	3.50	0.335	4	WHITE
H150X034F1T	A	1.50	3.50	0.335	1	WHITE
H075X034F1T	B	0.75	3.50	0.335	2	WHITE
H200X034F2T	A	2.00	3.50	0.335	1	YELLOW
H100X034F2T	B	1.00	3.50	0.335	2	YELLOW
H050X034F2T	C	0.50	3.50	0.335	4	YELLOW
H200X034F1T-B	A	2.00	3.50	0.335	1	WHITE
H100X034F1T-B	B	1.00	3.50	0.335	2	WHITE
H050X034F1T-B	C	0.50	3.50	0.335	4	WHITE

NOTE:
1. SEE MFG. DRAWING NO: A61183.

000472FK_C10220_HNUMX034F×T_00.PRT									
PANDUIT CORP. TINLEY PARK, ILLINOIS									
H***X034F** OPTIMUM COMPUTER PRINTABLE HEAT SHRINK MARKERS									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.XX) ± .031 (1.000) ± .010 (.XX) ± .031 (1.000) ± .010									
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION									
DRAWN BY RVU DATE 9-29-04					SCALE MAY 1:1 GMHS				
D 2-24-04 RVU DRAWING RELEASE.					0000 R				
REV DATE BY CHK DESCRIPTION					ECN - R CUST SUP QM5H				
C10220					C				