


## Dimensions: mm (In.)



| Mouser Stock No. | Type    | Circuit              | Button Color |
|------------------|---------|----------------------|--------------|
| 103-7035-EV      | 2P SPST | ON-OFF               | Black        |
| 103-7036-EV      | 3P SPST | ON-OFF (Illuminated) | Red          |
| 103-7037-EV      | 3P SPDT | ON-ON                | Black        |

**Electrical Specifications:**

- Rating: 10A/125VAC, 6A/250VAC, 10A/12VDC
- Contact Resistance: 50m  $\Omega$  max.
- Insulation Resistance: 500 VDC 100M  $\Omega$  min.
- Dielectric Strength: 1000 VAC 1 minute

**Mechanical Specifications:**

- Neon Lamps (103-7036-EV): 110VAC

**Rocker Switches**

103-7035-EV, 103-7036-EV, 103-7037-EV

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[103-7037-EV](#) [103-7035-EV](#) [103-7036-EV](#)