





LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
AD	0				T	SUPSD 2--5 PER 0160-4756-95	7-11-96	WS
					U	REV PER EC 0320-138-97	07 MAY 97	GJ
					V	SUPSD -21,-23 AND 085 -25,-43 PER EC 0630-146-99	17 APR 00	SR

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
- 3


TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 4

TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 5

SEE RESTRICTED CUSTOMER DRAWING 4-641606-3.



SECTION A-A
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

SUPSD BY 390262-5	OBsolete				5
	OBsolete	TINNED	PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641606-5
		3	PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641606-4
		2	PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641606-3
SUPSD BY 390262-5		1	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641606-2
		0	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641606-1
CONTACT FINISH		CONTACT MAT'L		HOUSING MATERIAL	
				PART NO.	

			PART NO		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ±. 3 PL DEC ±.005 ANGLES ±0°30'	DR		8-17-87		
	M.CYRUS		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK				
	R.MILLER		NAME		
	APPD		SOCKET ASSY, DIP, LADDER, 40 POS, DIPLOMATE DL		
MATERIAL	J.LAMBERT				
	APPD				
	-				
SEE TABLE	PRODUCT SPEC				
	108-1066				
FINISH	APPLICATION SPEC		SIZE	FSCM NO	DRAWING NO
	114-1049		D	00779	641606
	WEIGHT				
SEE TABLE	-		SCALE 5:1		SHEET 1 OF 1