

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0508667226

Status:

Obsolete

Description:

Ring Tongue Terminal for 300-350MCM AWG, Closed Uninsulated Brazed Barrel, Stud Size 7/8" (M20), Oxygen-Free Copper, Length 86.80mm (3.417")

Documents:

Drawing (PDF)

General	
Product Family	Ring and Spade Terminals
Series	50866
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	7/8" (M20)
Wire Size AWG	300MCM, 350MCM
Wire Size mm²	152.05 - 192.6
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-50866-002
Sales Drawing	SD-50866-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50866Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Tool Kit For 57343-9012	0573439001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION