






Dimensions: mm (IN)





101-0361



101-0461



PCB Hole Layout

**Mechanical Specifications:**

- Mechanical life: 500,000 cycles
- Operating temperature: -25° ~ +70°C
- Operating force: 130 ±50gf

Soldering Process:

- Temperature: 255°C max. for 5 sec.

Electrical Specifications:

- Rating: 50mA/12VDC
- Insulation resistance: >100MΩ @ 250VDC
- Dielectric Strength: 250VAC for 1 minute
- Contact resistance: <100MΩ
- Electrical life: 300,000 cycles

Materials:

- Contact: phosphor bronze silver plated

Note:

- H: .276" (101-0361), .374" (101-0461)

Tactile Switches (Thru-Hole)
101-0361, 101-0461

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-0461](#) [101-0361](#)