

We've Got an All-Star Lineup...
And We'll Keep Right On Growing



sub-2.5-inch	3-inch	3.5-inch	3.7-inch	4.0-inch	4.2-inch	4.3-inch	5.0-inch	5.7-inch	6.4-inch	6.5-inch	7.0-inch	8.0-inch
8.4-inch	8.5-inch	9.0-inch	10.1-inch	10.4-inch	12.1-inch	15.0-inch	15.6-inch	19.0-inch	20.1-inch	23.1-inch	23.5-inch	

LQ170M1LG1K

16 - 24 inch / 41 - 63 cm

Active Area (W x H):	365.76 x 228.6 mm
Backlight System:	CCFL
Brightness:	270 nits
Contrast Ratio:	450:1
Description:	Wide Panel
Diagonal Size:	16.9 inch (43.0 cm)
Display Mode:	Normally White
Family:	LQ170M1LG1K
Interface:	LVDS
Operating Temperature Range:	0°C to 45°C
Outline Dimensions (W x H x D):	382.2 x 246.8 x 10.3 mm
Pixel Format:	1920 x 1200
RoHS:	Yes
Storage Temperature Range:	-25°C to 60°C
Viewing Angle - 12 o'clock:	70 °
Viewing Angle - 6 o'clock:	60 °
Viewing Angle - side to side:	160 °

Distributor Inventory

Part Number	Distributor	Quantity	Inv. Date
-------------	-------------	----------	-----------

Documentation

There are no matching documents for this product or criteria.

Can't find the document you are looking for? Please contact your local [Sharp Microelectronics representative](#) for assistance.