



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	RELEASED	JWM	8/5/03	HO		DJC	

NOTES:

IEC61010 Ratings
1000V CAT III
6 Amps




Reinforced or Double Insulation

Materials:

Body - Polymide (Nylon) and Santoprene
Tip - Steel, Nickel Plated

Internal Resistance: <50 milliohms

Temperature: -20°C to 80°C



Pincer style contact can grasp terminals up to .16 [4mm] and can be rotated for easy connection. Flexible shaft is bendable to ±90°.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	8/6/03
CHECKED BY:	DATE:
Hisham Odish	
APPROVED BY:	DATE:
Daniel Carey	

DRAWING TITLE: Pincer Style Flexible Clip w/4mm Safety Jack, Black			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	76-061	16F7728.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	